

**PHILIPS**

Reflector

LED

13.5 W

E26

Green

046677568283



## State-of-the-art LED for the home

Party light for creating nice atmosphere at home

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Bulb Material: Glass

## Bulb dimensions

- Height: 13.2 cm
- Width: 12.2 cm

## Design and finishing

- Material: Glass

## Durability

- Nominal lifetime: 10,950 hour(s)
- Number of switch cycles: 10,000
- Ambient temperature range: -4 °F to 113 °F

## Light characteristics

- Color rendering index (CRI): -
- Warm-up time to 60% light: 0.5 s

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677568283
- EOC: 568287
- Product title: 13.5PAR38/PER/  
GREEN/G/E26/ND/ULW 3/1PF

## Power

- Power Factor (Fraction): 0.5

## Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 13.5 W
- Power Consumption: 13.5 W

## Product dimensions and weight

- Length: 13.2 cm

## Rated values

- Rated lifetime: 10,950 hour(s)

## Technical specifications

- Frequency: 60 Hz
- Dimmable: No
- Line Frequency: 60 Hz
- Cap-Base: E26 | Single Contact  
Medium Screw
- UL Wet/ damp/ dry location: Wet  
location

## Packaging dimensions and weight

- EAN/UPC – product: 046677568283
- Net weight: 0.35 kg
- Gross weight: 0.44 kg
- Height: 20.9 cm
- Length: 13 cm
- Width: 13 cm
- Material number (12NC):  
929001306763



Issue date: 2024-02-05  
Version: 0.56

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)