

# PHILIPS

Reflector  
(Dimmable)

LED

13W-120W

E26

Bright White

Dimming

046677568320



## Dimmable LED spot with a focused bright beam

Philips dimmable LED PAR spot light lamps are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern

lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

## Bulb dimensions

- Height: 12.9 cm
- Weight: 0.374 kg
- Width: 12.2 cm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 1200 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 930 | CCT of 3000K

## Other characteristics

- Lamp current: 120 mA
- Efficacy: 92 lm/W

## Packaging information

- EAN: 046677568320
- EOC: 568329
- Product title: 13PAR38/PER/930/G/E26/F40/D/UL W/T 4/1PF

#### Power consumption

- Energy Star Certified: Yes
- Power factor: 0.9
- Voltage: 120 V
- Wattage: 13 W
- Wattage equivalent: 120 W

#### Product dimensions & weight

- Length: 12.9 cm

#### Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 1200 lumen
- Rated peak intensity: 2500 cd
- Rated power: 13 W

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 046677568320
- Net weight: 0.350 kg
- Gross weight: 0.442 kg
- Height: 20.900 cm
- Length: 13.000 cm
- Width: 13.000 cm
- Material number (12NC):  
929003030103



Issue date: 2022-08-08  
Version: 0.48

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)