

PHILIPS

Bulb


LED

4W-40W

E26

Orange

046677568849



Brighten your home with infinite possibilities.

Philips LED energy-saving colored bulbs provide instant brightness and make colors appear more vivid. Ideal for special activities and occasions.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Saves up to 80% Energy

Light beyond illumination

- Colored Bulbs Classic Glass

Highlights

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Brilliant Colors (Glass)

Festive LED colored bulbs to decorate your home with bright colors for holidays and special occasions. Colored glass ensures high saturation for even brighter colors, for use both indoor and out.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Bulb Finish: Orange
- Bulb Material: Glass

Bulb dimensions

- Height: 10.6 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000
- Ambient temperature range: -4 °F to 113 °F

Light characteristics

- Warm-up time to 60% light: 0.5 s

Miscellaneous

- EyeComfort: Yes

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 046677568849
- EOC: 568840
- Product title: 4A19/PER/ORANGE/G/E26/ND 4/IPF

Power

- Power Factor (Fraction): 0.40

Power consumption

- Energy Star Certified: No
- Power factor: 0.4
- Voltage: 120 V
- Wattage: 4 W
- Wattage equivalent: 40 W
- Power Consumption: 4 W

Product dimensions and weight

- Length: 10.6 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 60 Hz
- Dimmable: No
- Line Frequency: 60 Hz
- Cap-Base: E26 | Single Contact
Medium Screw
- UL Wet/ damp/ dry location: Wet
location

Packaging dimensions and weight

- EAN/UPC – product: 046677568849
- Net weight: 0.03 kg
- Gross weight: 0.09 kg
- Height: 17.1 cm
- Length: 6.5 cm
- Width: 7.5 cm
- Material number (12NC):
929001937153



Issue date: 2024-02-05
Version: 0.22

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com