

# PHILIPS

Reflector  
(Dimmable)

LED

5.5W-50W

E26

Warm Glow

Dimming

046677570705



## The more you dim, the warmer the light

Not all LEDs dim the same. Philips dimmable LED PAR30L spot light bulbs with a warm glow effect work like halogen bulbs by getting warmer in tone when dimmed. Other LED bulbs simply get less bright, without a cozy glow.

### Light beyond illumination

- Dimmable
- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Instant on

**Designed for the comfort of your eyes**



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26

## Bulb dimensions

- Height: 8.35 cm
- Width: 6.4 cm

## Durability

- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2200–2700 K
- Nominal luminous flux: 500 lm
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K–2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677570705
- EOC: 570705
- Product title: 5.5PAR20/PER/927-22/F40/WG/G/T20 4/1PF

## Power consumption

- Energy Star Certified: Yes
- Power factor: 0.9
- Voltage: 120 V
- Wattage: 5.5 W
- Wattage equivalent: 50 W

## Product dimensions and weight

- Length: 8.35 cm

## Rated values

- Rated peak intensity: 800 cd

## Technical specifications

- Frequency: 50–60 Hz

## Packaging dimensions and weight

- EAN/UPC – product: 046677570705
- Net weight: 0.12 kg
- Gross weight: 0.16 kg
- Height: 14.6 cm
- Length: 7 cm
- Width: 7.5 cm
- Material number (12NC): 929003026705



Issue date: 2024-02-02  
Version: 0.28

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)