

PHILIPS

Reflector
(Dimmable)

LED

8.5W-75W

E26

Bright White

Dimming

046677570729



Dimmable LED spot with a focused bright beam

Philips dimmable LED PAR spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

Light beyond illumination

- Dimmable
- Instant on

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Instant on

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26

Bulb dimensions

- Height: 9 cm
- Width: 9.4 cm

Durability

- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 850 lm
- Warm-up time to 60% light: instant full light
- Color Code: 930 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 100 lm/W

Packaging information

- EAN: 046677570729
- EOC: 570721
- Product title:
8.5PAR30S/PER/930/F40/DIM/
GULW/T20 4/IPF

Power consumption

- Energy Star Certified: Yes
- Power factor: 0.9
- Voltage: 120 V
- Wattage: 8.5 W
- Wattage equivalent: 75 W

Product dimensions and weight

- Length: 9 cm

Rated values

- Rated peak intensity: 1600 cd

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 046677570729
- Net weight: 0.2 kg
- Gross weight: 0.28 kg
- Height: 20.9 cm
- Length: 10.2 cm
- Width: 13 cm
- Material number (12NC):
929003028105



Issue date: 2024-02-02
Version: 0.26

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com