

PHILIPS

Capsule

LED

3W-25W

G9

Bright White

046677570903



A familiar beam meets an innovative design

This Mains voltage LED capsule provides bright, all around, white light.

High quality light

- Bright white light

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Create the right light for your home

- A simple LED for everyday use

Highlights

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional capsule
- Socket: G9

Bulb dimensions

- Height: 5.3 cm
- Width: 1.77 cm

Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Efficacy (rated) (Nom): 83.00 lm/W
- Luminous Flux: 250 lm

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 83 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677570903
- EOC: 570903
- Product title: 3T3/PER/830/ND/G9/120V 6/1PF

Power

- Power Factor (Fraction): 0.5

Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 3 W
- Wattage equivalent: 25 W
- Power Consumption: 3 W

Product dimensions and weight

- Length: 5.3 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Dimmable: No
- Line Frequency: 50 to 60 Hz
- Cap-Base: G9

Packaging dimensions and weight

- EAN/UPC - product: 046677570903
- Net weight: 0 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 7.5 cm
- Material number (12NC):
929001266835



Issue date: 2024-02-06
Version: 0.50

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com