PHILIPS

Bulb

LED

16W-75W

E26

Daylight Deluxe

046677571825

Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

High quality light
- Long life bulb - Lasts up to 10 years

Choose for a sustainable solution
- Saves up to 80% Energy

Create the right light for your home
- A simple LED for everyday use

Highlights

10,950-hour rated average life
With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

A Simple LED for Everyday Use
The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Saves up to 80% Energy

Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

Specifications

Bulb characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: E26
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions
- Height: 7.7 cm
- Width: 15 cm

Durability
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000
- Ambient temperature range: -20 °C to 45 °C

Light characteristics
- Beam angle: 120 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 865 | CCT of 6500K
- Correlated Color Temperature (Nom): 6500 K
- Luminous Efficacy (rated) (Nom): 75 lm/W
- Luminous Flux: 1,200 lm

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Efficacy: 75 lm/W
- EU RoHS compliant: Yes

Packaging information
- EAN: 046677571825
- EOC: 571828
- Product title: 16UFO/PER/865/FR/P/E26/ND 4/1PF

Power
- Power Factor (Fraction): 0.5

Power consumption
- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 110-240 V
- Wattage: 16 W
- Wattage equivalent: 75 W
- Power Consumption: 16 W

Product dimensions and weight
- Length: 7.7 cm

Rated values
- Rated lifetime: 15,000 hour(s)

Technical specifications
- Frequency: 50-60 Hz
- Dimmable: No
- Line Frequency: 50 to 60 Hz
- Cap-Base: E26 | Single Contact Medium Screw

Packaging dimensions and weight
- EAN/UPC - product: 046677571825
- Net weight: 0.14 kg
- Gross weight: 0.15 kg
- Height: 15.5 cm
- Length: 15.5 cm
- Width: 8.5 cm
- Material number (12NC): 929002010625

Issue date: 2024-02-05
Version: 0.30

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com