

# PHILIPS

Reflector

LED

10W-90W

E26

Bright White

046677573171



## State-of-the-art LED for the home

Philips LED PAR spot light lamp are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26

## Bulb dimensions

- Height: 12.9 cm
- Width: 12.2 cm

## Durability

- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 900 lm
- Warm-up time to 60% light: instant full light
- Color Code: 930 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677573171
- EOC: 573170
- Product title:  
10PAR38/930/G/E26/F40/ND/ULW  
T20 4/1PF

## Power consumption

- Energy Star Certified: No
- Power factor: 0.8
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

## Product dimensions and weight

- Length: 12.9 cm

## Rated values

- Rated peak intensity: 1533 cd

## Technical specifications

- Frequency: 50-60 Hz



Issue date: 2024-02-02  
Version: 0.52

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)