

PHILIPS

Bulb

LED

8.8W-60W

E26

Soft White

046677573232



Dusk to Dawn

Philips LED Dusk to Dawn bulb is designed to save even more energy than regular LED by turning itself on and off with the level of daylight - providing secure light during the night, and turning off with the light of day.

Light beyond illumination

- Built-in automatic on/off light sensor

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Day and night sensor



With its built-in automatic light sensor, this bulb switches on automatically after dusk and off after dawn.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted

Bulb dimensions

- Height: 10.98 cm
- Width: 6.15 cm

Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 220 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 90.00 lm/W
- Luminous Flux: 800 lm

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 90 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677573232
- EOC: 573238
- Product title: 8.8A19/PER/927/FR/P/E26/D2D/T20 4/IPF

Power

- Power Factor (Fraction): 0.7

Power consumption

- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8.8 W
- Wattage equivalent: 60 W
- Power Consumption: 8.8 W

Product dimensions and weight

- Length: 10.98 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 60 Hz
- Dimmable: No
- Line Frequency: 60 Hz
- Cap-Base: E26 | Single Contact Medium Screw
- UL Wet/ damp/ dry location: Damp location

Packaging dimensions and weight

- EAN/UPC – product: 046677573232
- Net weight: 0.06 kg
- Gross weight: 0.09 kg
- Height: 17.1 cm
- Length: 6.5 cm
- Width: 7.5 cm
- Material number (12NC): 929002333693



Issue date: 2024-02-06
Version: 0.44

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com