

PHILIPS

Bulb (Dimmable)

LED

6.6W-60W

E12

Warm Glow

Dimming

046677573393



Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E12
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 9.2 cm
- Weight: 0.025 kg
- Width: 4.75 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 300 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 95
- Color temperature: 2200-2700 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 750 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: poc
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 65 mA
- Efficacy: 113 lm/W

Packaging information

- EAN: 046677573393
- EOC: 573394
- Product title: 6.6A15/PER/UD/CL/G/E12/WGD6/2PF T20

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 6.6 W
- Wattage equivalent: 60 W

Product dimensions & weight

- Length: 9.2 cm

Rated values

- Rated beam angle: 300 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 750 lumen
- Rated power: 6.6 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677573393
- Net weight: 0.032 kg
- Gross weight: 0.054 kg
- Height: 14.600 cm
- Length: 5.500 cm
- Width: 10.000 cm
- Material number (12NC):
929003084603



Issue date: 2022-09-16
Version: 0.45

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com