

# PHILIPS

Bulb (Dimmable)

LED


4.4W-40W

E26

Soft White

Dimming

046677573980



## State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light


- True incandescent-like warm white light

### Designed to be seen, looks good on and off

- Classic glass LED

# Highlights

## Incandescent-like warm white



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design

## Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

# Specifications

## Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Clear
- Bulb Finish: Clear

## Bulb dimensions

- Height: 13.7 cm
- Width: 6.4 cm

## Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 400 lm
- Warm-up time to 60% light: instant full light
- Color Code: 927 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 90 lm/W

## Packaging information

- EAN: 046677573980
- EOC: 573989
- Product title: 4.4ST19/VIN/927/CL/G/E26/DIM 4/4PF T20

## Power consumption

- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4.4 W
- Wattage equivalent: 40 W

## Product dimensions and weight

- Length: 13.7 cm

## Technical specifications

- Frequency: 60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 046677573980
- Net weight: 0.18 kg
- Gross weight: 0.3 kg
- Height: 17.9 cm
- Length: 7 cm
- Width: 27.5 cm
- Material number (12NC): 929002990433



Issue date: 2024-02-04  
Version: 0.46

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)