PHILIPS

Bulb (Dimmable)

LED


6.5W-60W

E26

Amber Light

Dimming

046677574093



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light
- Amber light

Designed to be seen, looks good on and off
- Vintage style LED

Highlights

2000K
This bulb has a color temperature of 2000K, providing you with an extra warm and intimate atmosphere. Ideal for home lighting design.

Vintage (2000K & 2200K)
Imagine the vintage look of traditional lighting with the benefits of LED. With Philips Vintage LED filament bulbs, you can have the classic look you love, with the energy-efficiency you need. Gives the traditional color and amber glow of old-fashioned incandescent lighting. The clear amber tinted glass bulb, brass finish base, and retro styling of the LED filament add a vintage flair to the decorative lighting in your home. The intricate swirling filament offers a cozy and warm ambience.

Specifications

Bulb characteristics
- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Amber

Bulb dimensions
- Height: 10.5 cm
- Weight: 0.028 kg
- Width: 6 cm

Durability
- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics
- Beam angle: 330 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Light Color Category: Amber Light
- Nominal luminous flux: 400 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 820 | CCT of 2000K

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Lamp current: 75 mA
- Efficacy: 61 lm/W

Packaging information
- EAN: 046677574093
- EOC: 574095
- Product title: 6.5A19/VIN/820/E26/ Amber/G/SP D 4/1PFT20

Power consumption
- Energy Star Certified: No
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 6.5 W
- Wattage equivalent: 60 W

Product dimensions & weight
- Length: 10.5 cm

Rated values
- Rated beam angle: 330 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 400 lumen
- Rated power: 6.5 W

Technical specifications
- Frequency: 60 Hz

Issue date: 2023-11-07
Version: 0.48

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com