PHILIPS

Bulb (Dimmable)

LED

8W-60W

E26

Warm Glow

Dimming

046677574888



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics
- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Bulb Material: Glass

Bulb dimensions
- Height: 10.5 cm
- Width: 6 cm

Design and finishing
- Material: Glass

Durability
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics
- Beam angle: 300 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 2700-2200 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: instant full light
- Color Code: 927-922 | CCT of 2700K-2200K

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Efficacy: 100 lm/W

Packaging information
- EAN: 046677574888
- EOC: 574889
- Product title: 8A19/PER/UD/FR/G/E26/WGD 4/3PFT20

Power consumption
- Energy Star Certified: Yes
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8 W
- Wattage equivalent: 60 W

Product dimensions and weight
- Length: 10.5 cm

Technical specifications
- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677574888
- Net weight: 0.1 kg
- Gross weight: 0.15 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 18.5 cm
- Material number (12NC): 929003083235

Issue date: 2024-02-02
Version: 0.51

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com