

PHILIPS

Bulb (Dimmable)

LED


5.5W-60W

E26

Bright White

Dimming

046677575090



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 13.7 cm
- Weight: 0.048 kg
- Width: 6.4 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 330 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 500 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 930 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 62 mA
- Efficacy: 90 lm/W

Packaging information

- EAN: 046677575090
- EOC: 575092
- Product title:
5.5ST19/VIN/930/E26/CL/G/SP D
2PF T20

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 5.5 W
- Wattage equivalent: 60 W

Product dimensions & weight

- Length: 13.7 cm

Rated values

- Rated beam angle: 330 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 500 lumen
- Rated power: 5.5 W

Technical specifications

- Frequency: 60 Hz



Issue date: 2023-11-07
Version: 0.48

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com