

PHILIPS

Bulb (Dimmable)

LED


7.5W-40W

E26

Amber Light

Dimming

046677575229



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Designed to be seen, looks good on and off

- Looks good on and off
- Vintage style LED

Highlights

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

Vintage (2000K & 2200K)

Imagine the vintage look of traditional lighting with the benefits of LED. With Philips Vintage LED filament bulbs, you can have the classic look you love, with the energy-efficiency you need. Gives the traditional color and amber glow of old-fashioned incandescent lighting. The clear amber tinted glass bulb, brass finish base, and retro styling of the LED filament add a vintage flair to the decorative lighting in your home. The intricate swirling filament offers a cozy and warm ambience.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional capsule
- Socket: E26
- Bulb Finish: Amber
- Bulb Material: Glass

Bulb dimensions

- Height: 28.5 cm
- Width: 20 cm

Design and finishing

- Material: Glass

Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000
- Ambient temperature range: -4 °F to 104 °F

Light characteristics

- Beam angle: 330 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2000 K
- Nominal luminous flux: 400 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 820 | CCT of 2000K
- Correlated Color Temperature (Nom): 2000 K
- Luminous Efficacy (rated) (Nom): 53 lm/W
- Luminous Flux: 400 lm

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 53 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677575229
- EOC: 575225
- Product title: 7.5G63/VIN/820/CL/G/E26/amber/SP/DIM 1CT

Power

- Power Factor (Fraction): 0.7

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 7.5 W
- Wattage equivalent: 40 W
- Power Consumption: 7.5 W

Product dimensions and weight

- Length: 28.5 cm

Rated values

- Rated lifetime: 15,000 hour(s)

Technical specifications

- Frequency: 50-60 Hz
- Dimmable: Only with specific dimmers
- Line Frequency: 50 to 60 Hz
- Cap-Base: E26 | Single Contact Medium Screw
- UL Wet/ damp/ dry location: Wet location

Packaging dimensions and weight

- EAN/UPC – product: 046677575229
- Net weight: 0.36 kg
- Gross weight: 0.7 kg
- Height: 32 cm
- Length: 22.5 cm
- Width: 22.5 cm
- Material number (12NC): 929001936313



Issue date: 2024-01-20
Version: 0.54

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com