

# PHILIPS

Reflector  
(Dimmable)

LED

10.5W-75W

E26

2200-3000

Dimming

046677575953



## The more you dim, the warmer the light

Not all LEDs dim the same. Philips dimmable LED PAR30L spot light lamp with a warm glow effect work like halogen spots by getting warmer in tone when dimmed. Other LED bulbs simply get less bright, without a cozy glow.

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern

lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

## Bulb dimensions

- Height: 9 cm
- Weight: 0.209 kg
- Width: 9.4 cm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 95
- Color temperature: 2200-3000 K
- Nominal luminous flux: 850 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 2200-3000

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 95 mA
- Efficacy: 80 lm/W

## Packaging information

- EAN: 046677575953
- EOC: 568311
- Product title:  
10.5PAR30S/PER/UD/30/G/F40/WG  
/T 4/1PF

#### Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10.5 W
- Wattage equivalent: 75 W

#### Product dimensions & weight

- Length: 9 cm

#### Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 850 lumen
- Rated peak intensity: 1315 cd
- Rated power: 10.5 W

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 046677575953
- Net weight: 0.196 kg
- Gross weight: 0.278 kg
- Height: 20.900 cm
- Length: 10.200 cm
- Width: 13.000 cm
- Material number (12NC):  
929003118903



Issue date: 2022-08-08  
Version: 0.50

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)