

# PHILIPS

Reflector  
(Dimmable)

LED

10.5W-75W

E26

Daylight

Dimming

046677575977



## Dimmable LED spot with a focused bright beam

Philips dimmable LED PAR spot light lamps are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern

lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Instant on

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26

## Bulb dimensions

- Height: 11.6 cm
- Width: 9.4 cm

## Durability

- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color rendering index (CRI): 95
- Color temperature: 5000 K
- Nominal luminous flux: 850 lm
- Warm-up time to 60% light: instant full light
- Color Code: 950 | CCT of 5000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 80 lm/W

## Packaging information

- EAN: 046677575977
- EOC: 568345
- Product title: 10.5PAR30L/PER/UD/50/G/E26/F40/D/T 4/1PF

## Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10.5 W
- Wattage equivalent: 75 W

## Product dimensions and weight

- Length: 11.6 cm

## Rated values

- Rated peak intensity: 1315 cd

## Technical specifications

- Frequency: 50-60 Hz

**Packaging dimensions and weight**

- EAN/UPC – product: 046677575977
- Net weight: 0.24 kg
- Gross weight: 0.3 kg
- Height: 20.9 cm
- Length: 10.2 cm
- Width: 13 cm
- Material number (12NC): 929003118703



Issue date: 2024-02-02  
Version: 0.52

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)