

PHILIPS

Reflector
(Dimmable)

LED

10W-75W

E26

Bright White

Dimming

046677575991



Dimmable LED spot with a focused bright beam

Philips dimmable LED PAR spot light lamps are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for general and flood lighting.

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Light beyond illumination

- Instant on

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern

lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Instant on

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 8.3 cm
- Weight: 0.126 kg
- Width: 6.4 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 95
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 800 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 930 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 88 mA
- Efficacy: 80 lm/W

Packaging information

- EAN: 046677575991
- EOC: 573196
- Product title:
10PAR20/PER/UD/30/G/F40/D/T20
/HO 4/1PF

Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 75 W

Product dimensions & weight

- Length: 8.3 cm

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated peak intensity: 1270 cd
- Rated power: 10 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677575991
- Net weight: 0.120 kg
- Gross weight: 0.156 kg
- Height: 14.600 cm
- Length: 7.000 cm
- Width: 7.500 cm
- Material number (12NC):
929003119203



Issue date: 2022-08-08
Version: 0.50

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com