

# PHILIPS

Linear tubeYes - Check ballast compatibility

LED

24W-54W

G5

3000/4000/5000

046677580223



## Bright LED lighting with excellent light quality

Upgrading to Philips LED tubes is a fast and easy way to replace your old fluorescent tubes with modern and efficient LED technology. Select desired color temperature via switch before installing the LED tube.

### **Choose a simple replacement for your old bulbs**

- Compatible with most instant-start electronic ballasts

### **Choose for a sustainable solution**

- Long life bulb - Lasts up to 50 years

# Highlights

## InstantFit Ballast Compatibility

Philips InstantFit LED tubes have been tested and operated to work on more ballast types than competitive products in the market. Check the compatibility list here (link to <http://images.philips.com/is/content/>

PhilipsConsumer/PDFDownloads/United%20States/ODLI20180301\_001-UPD-en\_US-PLt-16118CR\_InstantFit\_Ballast-Compatibility-Guide\_2018-1.pdf)

## Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

# Specifications

## Bulb characteristics

- Dimmable: Yes – Check ballast compatibility
- Intended use: Indoor
- Lamp shape: T5
- Socket: G5

## Bulb dimensions

- Height: 116.3 cm
- Width: 1.86 cm

## Durability

- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000/4000/5000 K
- Nominal luminous flux: 3100/3300/3300 lm
- Warm-up time to 60% light: instant full light
- Color Code: 3000K/4000K/5000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 137 lm/W

## Packaging information

- EAN: 046677580223
- EOC: 580225
- Product title: 24T5HO/LED/46-3CCT/IF33/G/DIM 10/1 FB

## Power consumption

- Power factor: 0.9
- Voltage: 39-64 V
- Wattage: 24 W
- Wattage equivalent: 54 W

## Product dimensions and weight

- Length: 116.3 cm

## Service

- Warranty: 5 year(s)

## Technical specifications

- Frequency: VA51018828 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 046677580223
- Net weight: 0.15 kg
- Gross weight: 0.23 kg
- Height: 117.5 cm
- Length: 2.5 cm
- Width: 2.5 cm
- Material number (12NC): 929003554805



Issue date: 2023-11-22  
Version: 0.37

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)