

# PHILIPS

Bulb


LED

4W-60W

E26

Daylight

046677580513



## Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Better for your wallet and your planet
- Long life bulb - Lasts up to 50 years

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Long life bulb - Lasts up to 50 years

With a lifetime of up to 50,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 50 years.

## Saving up to 90% energy

LED technology saves up to 90% energy compared to your standard bulb. It therefore pays for itself and saves you money year after year. It also helps protect the environment.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Clear

## Bulb dimensions

- Height: 11 cm
- Weight: 0.039 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 100,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 850 | CCT of 5000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 85 mA
- Efficacy: 200 lm/W

## Packaging information

- EAN: 46677580513
- EOC: 580514
- Product title: 4A19/UE/850/CL/G/E26/ND 1PF/2

## Power consumption

- Energy Star Certified: No
- Power factor: 0.4
- Voltage: 120 V
- Wattage: 4 W
- Wattage equivalent: 60 W

## Product dimensions & weight

- Length: 11 cm

## Rated values

- Rated lifetime: 50,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated peak intensity: N/A cd
- Rated power: 4 W

## Technical specifications

- Frequency: 60 Hz

**Packaging dimensions and weight**

- EAN/UPC – product: 046677580513
- Net weight: 0.039 kg
- Gross weight: 0.073 kg
- Height: 17.100 cm
- Length: 6.550 cm
- Width: 7.550 cm
- Material number (12NC): 929003536203



Issue date: 2023-11-08  
Version: 0.43

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)