

PHILIPS

Camill Wall Light 3W

Outdoor luminaires

Black

Solar wall light



046677582937



Our most energy-efficient LED lights yet

Give your outdoor wall a heritage look, with the black Philips LED outdoor wall light. Its diffused, bright light is also ideal for lighting up your front entrance. Its retro design is a stylish way to enjoy your outdoor moments.

Ease of use

- A full range of available applications

Easy installation

- No wiring required

Sustainable light solutions

- Ultra Efficient Solar

Special characteristics

- Motion and Dusk-to-dawn sensor integrated

Highlights

A full range of available applications

Ideal outdoor lighting for a garden, terrace, pathway or balcony, Philips outdooras wall, post, pedestal and ceiling lights create a cosy, relaxing atmosphere when the sun goes down, as well as providing the reassurance of being able to see safely after dark.

No wiring required

This light is powered entirely by solar energy. No wiring is needed, making these lights easy to position and reposition anywhere in your garden or other outdoor area.

Ultra Efficient Solar

With the Philips Ultra Efficient Solar system, these luminaires provide light for up to 25 hours on a fully-charged battery. Enjoy bright light all night, or even in bad or overcast weather conditions.

Motion and Dusk-to-dawn sensor integrated



With a built-in motion sensor, these lights automatically welcome you when you return home after dark, or light up when visitors arrive. The unique dusk-to-dawn feature turns the lights on automatically when it gets dark outside--perfect for those long summer evenings or to ensure your safety.

Specifications

Design and finishing

- Color: Black
- Material: Plastic

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- click!FIX mounting: Yes
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: Yes
- Motion sensor: Yes
- Solar Energy: Yes
- Warm White Light: No
- Centerpiece: No

Garden area

- Garden area: Garden & Patio

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No

Product dimensions and weight

- Net weight: 0.55 kg
- Height: 20.6 cm
- Length: 19 cm
- Width: 14 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 250/20
- Light color: 3000
- Mains power: 4 V
- Energy class included light source: not applicable
- Maximum wattage replacement bulb: 25 W
- IP code: UL03 – Wet Location (North America)
- Class of protection: Class III

- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC – product: 046677582937
- Net weight: 0.55 kg
- Gross weight: 0.82 kg
- Height: 24 cm
- Length: 17.5 cm
- Width: 17.5 cm
- Material number (12NC): 929003298503



Issue date: 2024-02-07
Version: 0.67

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com