

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____


Notes: _____

Ordering Guide

Example: 55 ABS 50H E

Product Code	55	HID Ceiling Canopy
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Wattage/Source	50H 70H 100H 150H 35S 50S 70S 100S 150S	50W MH 70W MH 100W MH 150W MH 35W HPS 50W HPS 70W HPS 100W HPS 150W HPS *1
Voltage	E F G H	120V 208V 240V 277V

*1 (E) 120V Option Only



Specifications

CONSTRUCTION:

Two piece cast aluminum ballast housing. Cast aluminum 2 1/2" dia. loop.

55 Accessories

HID ceiling canopy

Specifications

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

BALLAST:

Customer must specify source and wattage for ballast.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

