



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets					
	Open Downlight			Adjustable		Enclosed Diffuser
Reflector	Sloped Ceiling	Baffles	Basic White	Eyeball:		
1100IC	1144 1144CD	1131WH 1133WH 1154	1105 1105WH 1175 1176 1176WH	1171	1182	1124 1126 1128 1177SH 1178SH 1190
	Cone: 1113 1113CD 1113WH					Open Wet: 1184WH

# 1100IC Lytecaster INC 6 3/4"

## IC frame

### Features

- Housing:** 0.026" (#20 ga.) galvanized steel. U.L. listed for direct contact with thermal insulation. Access door for inspection of junction box.
- Mounting Frame:** 0.036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. ICM version has 3/8" deep integral lip. Four slots are positioned 90° apart to simplify alignment. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** 2" x 4" x 4", 0.063" (#14 ga.) galvanized steel. U.L. listed for, maximum of 6 No. 12 ga., 90°C through branch circuit conductors. Quick release "L" shaped cover for outside access to wiring. Access door inside of housing allows easy inspection of wiring without removal of housing. Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without the need for additional connectors.
- Mounting Bars:** 0.059" (#16 ga.) galvanized steel. 13" long bars extend to 27", rotatable and lockable, with integral T-bar tabs. Attach to wood joist or T-bar ceilings without need of accessories.
- Socket Housing:** Impact extruded aluminum or galvanized steel.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 leads to junction box.
- Thermal Protector:** Meets NEC and U.L. requirements. Located inside housing.

### Options & Accessories

- Mounting Bars:** 1976 - 13" set of (4)  
**Plaster Ceiling Ring:** 1961 - 7/8" depth for wet plaster ceilings.  
Not for use with ICM housing.

**Extra-Thick Ceiling Mounting Ring: 1967A** - up to 2" thick ceilings.

### Labels

**UL (Type I.C., Suitable for Damp Locations), I.B.E.W.**

**Romex® is a registered trademark of General Cable Industries Inc.**

