

Project: _____

Location: _____

Cat.No: _____

Type: _____


Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: 537 ABS A D 50H E B N

Product Code	537	Stockholm
Finish	ABS	Antique Brass
	ACP	Antique Copper
	ARD	Antique Red
	ASI	Antique Silver
	BLK	Black
	BRN	Brown
	BRZ	Bronze
	FGN	Forest Green
	GRA	Granite
	IRN	Ironstone
	RBZ	Rustic Bronze
	SRT	Shadow Rust
	VBZ	Verde Bronze
	VCP	Verde Copper
	VGN	Verde
VTC	Vintage Copper	
WBZ	Weathered Bronze	
WHT	White	
Panel/Globe	A	Clear Acrylic
Socket	D	Medium
	G	Mogul
	L	LED
Wattage/Source	50H	50W MH
	70H	70W MH
	35S	35W HPS
	50S	50W HPS
	70S	70W HPS
	100S	100W HPS
	100I	100W INC.
	LED	LED
Voltage	E	120V
	F	208V
	G	240V
	H	277V
Distribution	B	6" Type V Distrib.
	C	6" Type III Distrib.
	N	None
Photoeye	N	None



537 Stockholm

Side arm mount

Specifications

CONSTRUCTION:

Cast aluminum finial. Spun aluminum cap. Spun aluminum roof. 4 Cast aluminum crowns. Fluted cast aluminum top ring. 4 Cast aluminum legs. Cast aluminum refractor support. Cast aluminum cap. Cast aluminum "S" fluted bracket arm and wall plate.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

See lenses for available options.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Ballast and component parts mounted inside two-piece cast aluminum moisture proof ballast compartment. (Customer must specify wattage and voltage.)

MOUNTING:

See template for dimensions & mounting instructions.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

41 1/2"

Width:

19 3/8"

Projection:

22 1/4"

Top to Outlet:

29"

Max. Weight:

28 lbs.

