



Adjustable Above ground

Medians

Tree Lighting

Landscape Areas

Wall Wash

Building Accent

Sign Lighting

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications



Certifications ETL and CETL listed for wet location, direct burial, and concrete pour. Certified to IP65 and IP67 to ensure protection against the harshest environments. IEC compliant versions available, consult factory.

Direct Burial Housing 8 5/8" diameter direct burial pipe with provision for anti-rotation device.

Lamp/Ballast Housing Low copper heavy duty cast aluminum.

Splice Compartment Supplied with two 3/4" NPT conduit entrances. Suitable for through wiring.

Lens Standard 3/8" clear tempered flat borosilicate glass (F). Sealed to housing with high temperature injection molded silicone gasket. Optional linear spread lens available.

Lens Frame Heavy duty die cast bronze lens frame is supplied as standard. Fastened to housing with six captive 10-24 stainless steel Allen cap screws.

Reflectors Spun aluminum highly specular Alzak finish for either NEMA type 1 or 2 spot (SPT) or NEMA type 3 or 4 flood (FLD) distributions. Field adjustable up to 25° tilt and 360° horizontal rotation. NOTE: Tilt adjustment varies by lamp type. A segmented fluorescent reflector is available for up to 42W lamps.

Lamp Holder Porcelain 4kv pulse rated for HID and Incandescent lamp sources.

Options Cast aluminum Convex Rock Guard (CR), Directional Shield (DS), Internal Glare Shield (IGS), Internal Hex Cell Louver (HL), Glass Color Filter (GF), Die cast bronze Port Hole (PH).

Finish Housing Black (BK). Options can be painted in standard or custom colors. Powder Coat Standard.

Safety Caution: Care should be taken when specifying fixtures for use in pedestrian walkways to avoid problems that may be caused by high lens temperatures. Consult factory for more information.

Warning Caution: Care should be taken not to install in-ground fixtures in areas where water can stand for prolonged periods of time. Sufficient drainage must be provided to avoid problems. Consult factory for more information.

SL26 Composite Inground

CFL/INC/MH/HPS Inground

Product Order Guide

Example: SL-26-70MH-T6-277-SPT-F-BK-DB10-DS


Series	Max Watts	Lamp Type	Voltage ⁶	Optics	Lens	Finish ^{3,6}	DB ²	Options			
SL-26	Fluorescent										
	26CFT	CFT ¹	120	SPT ¹	Spot	F ¹	Clear Flat	BK ³ Black	DB-10"	CR ¹	Convex Rockguard ^{5,7}
	32CFT	CFT ¹	208			LS ¹	Linear Spread	BZ ³ Bronze	DB-14"	DS ¹	Directional Shield ^{5,7}
	42CFT	CFT ¹	240	WW ¹	Wallwash			WH ³ White	DB-18"	PH ⁴	Porthole
			277	FL ¹	Fluorescent			GR ³ Green	DB-24"	IGS ¹	Glare Shield
	High Pressure Sodium										
	50HPS	E17 ¹		NFLD ¹	Narrow Flood			NA ³ Nat Alum		HL	Hex Cell Louver
	70HPS	E17 ¹		MFLD ¹	Medium Flood			GY ³ Gray		GF	Glass Color Filter
								CC ³ Custom Color		LFSS ¹	Stainless Steel Lens Frame
											AHOT AIM-HOT™
	Metal Halide										
	50MH	E17 ¹									
	70MH	E17 ¹									
	70MH	Par30 ^{1,8}									
	39MH	Par20 ⁸									
	39MH	T6 or T4 ¹									
	70MH	T6 or T4 ¹									
	35MH	R111 ^{1,8}									
	20MH	BT5 ¹	120								
	20MH	T4 ¹	120/277								
	Incandescent/Halogen/Low Voltage										
	75INC	Par30 ^{1,8}	120								
	100INC	T4mini ¹	120								
	50INC	Par20 ⁸	120								
	75INC	MR16 ⁸	120/277/12								

- ¹ Not available with the PH Porthole option, use Par20 or MR16 only.
- ² Height above grade All units include an extra 18" or 457mm of tube for direct burial.
- ³ Powder coat standard.
- ⁴ The PH Porthole option is supplied as standard in die cast bronze.
- ⁵ These options are supplied in heavy wall cast aluminum.
- ⁶ Consult factory for other voltages and finishes.
- ⁷ Consult factory for cast bronze options.
- ⁸ Does not require internal optics.

CFT = triple biax
 Note: E17 Lamps 150W and below are medium base

Luminaire Dimensions

Luminaire	A		B		C		D		E		F		Weight	
	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	lbs.	kg
SL-26-F	6.95	177	0.75	19	10.00 min	254	18.00	457	n/a	n/a	8.62	219	37	17.8
SL-26-PH	6.95	177	0.75	19	14.00 min	355	18.00	457	3.35	85	8.62	219	40	18.1
SL-26-CR	6.95	177	0.75	19	18.00 min	457	18.00	457	1.00	25	8.62	219	37	17.8
SL-26-DS	6.95	177	0.75	19	24.00 min	609	18.00	457	3.85	98	8.62	219	37	17.8



Size	C min	C max
-10"	10"	20"
-14"	14"	28"
-18"	18"	38"
-24"	24"	48"

