

PHILIPS

Arbour Wall Light
6W

myGarden


Arbour

antracit

LED



16460/93/16



Enjoy a beautiful garden with light

Philips Arbour LED outdoor wall light in anthracite grey frames a panel of light within a durable die-cast aluminum surround. This picture of light will illuminate your outdoor space with plenty of diffuse warm white light.

Sustainable light solutions

- Energy saving
- High quality LED light
- Long operating life up to 25 years
- Warm white light
- Philips offers 5 year warranty on the LED module and driver

Designed for your garden

- IP44 - weather proof

Highlights

Energy saving




This Philips energy saving lamp conserves energy compared to traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light




The LED technology, integrated into this Philips lamp, is a uniquely developed solution by Philips. While instantly turned on, it enables an optimal light output and brings out vivid colors in your home.

Long operating life



A light source you can trust. The LED bulb, delivered with this Philips LED lamp, will last up to 25.000 hours (which equals 25 years on basis of an average use of 3 hours / day with an amount of at least of 13.000 on/off switching cycles). It feels so comfortable to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambiance in your home.

Warm white light



Light can have different color temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

5 year warranty on LED system



On top of the standard 2 year warranty for this lamp, Philips offers 5 year warranty on the LED system, meaning the LED module and the driver in this lamp.

IP44 - weather proof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water, this product is most common and ideal for general outdoor use.

Specifications

Design and finishing

- Color: Anthracite
- Material: Aluminium

Extra feature/accessory incl.

- 5 years warranty on the LED module: Yes
- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden & Patio

Miscellaneous

- Especially designed for: Garden & Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No

Packaging dimensions and weight

- EAN/UPC - product: 8718696131244
- Net weight: 0.67 kg
- Gross weight: 0.79 kg
- Height: 24.1 cm
- Length: 8.6 cm
- Width: 17.6 cm
- Material number (12NC): 915005193801

Product dimensions and weight

- Net weight: 0.670 kg
- Height: 22.1 cm
- Length: 16.6 cm
- Width: 7.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 25,000 hour(s)
- Total lumen output fixture: 600 lm
- Mains power: 50 Hz
- LED: Yes
- Energy class included light source: E
- Wattage bulb included: 6 W
- IP code: IP44
- Class of protection: Class II
- Light source replaceable: No
- Number of light sources: 1



Issue date: 2024-02-07
Version: 0.346

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com