

DESCRIPTION

The 144 series is a decorative pendant family with a conical form. This product is a tapered shape shade, with a variety of options to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, with 83+ CRI. The stem, canopy, and finial finishes are available in many painted options. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in three standard sizes, eleven standard fabrics and three vinyl materials, as well as the ability to customize, allowing the designer to select a look for any space.

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover available (TC).

5" diameter canopy with self aligning swivel. Stem is 1/2" aluminum tubing with threaded rod. Air craft cable option is 3/64" cable. Slope adapter option available (SCA-XX - 8°- 45°, but slope dimension must be provided).

24" Diameter

Standard length =
24" OAH (Overall Height)

Min	Max
12" OAH	96" OAH

30" Diameter

Standard length =
30" OAH (Overall Height)

Min	Max
14" OAH	96" OAH

36" Diameter

Standard length =
36" OAH (Overall Height)

Min	Max
16" OAH	96" OAH

Stem Options

Single Rigid Stem	-P1S
Single Stem Air Craft Cable	-P1SAC

Consult factory for non standard lengths under min and over 96".

Painted Finishes

ALP - Aluminum Paint
BM - Bronze Metallic
DP - Dark Platinum
GRM - Graphite Metallic
MB - Matte Black
MW - Matte White
CC - Custom Color - Specify
Consult factory for custom color.

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.Shade in Shade offers 2 material selections, overlapping each other.

Fabric Shade Selections

SIW - Silk White
SIY - Silk Ivory
SWH - Shantung White
SEG - Shantung Eggshell
SBG - Shantung Beige
GBB - Glynn Brussels Beige
LOLA - Lola Sand
NGS - Silk Glow
LCK - Linen Chopstick
LAT - Linen Alabaster
VLW - Verona Linen White

Vinyl Coated Fabric

ABR - Alabaster Vinyl
NFX - Natural Flax
GHY - Golden Honey
Note: For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended.

LEDs

LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated Lamp Life: 50,000 hrs

Catalog #		Type
Project		
Comments		Date
Prepared by		

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. All LED components are RoHS compliant. Drivers conform to FCC regulations. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.



144 SERIES

Diameter: 24"

- Delivered Lumens (@3500K):4080
- Wattage: 47W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K

Diameter: 30"

- Delivered Lumens (@3500K):4175
- Wattage: 47W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K

Diameter: 36"

- Delivered Lumens (@3500K):7045
- Wattage: 79W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K



ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)

Fixture Number: 144-24-P1S-L5/827-UNV-MW-24

Series ¹	Size	Mounting Type	LED Lamp			LED Voltage	Finish	Options ²	Overall Height (OAH)
144 = Conical Pendant	24 = 24" 30 = 30" 36 = 36"	P1S = Single Stem P1SAC = Single Stem with Aircraft Cable	24" L5/827 L5/830 L5/835 L5/840	30" L5/837 L5/830 L5/835 L5/840	36" L9/827 L9/830 L9/835 L9/840	UNV (120-277)	MW = Matte White MB = Matte Black BM = Bronze Metallic DP = Dark Platinum ALP = Aluminum Paint GRM = Graphite Metallic VLW = Verona Linen White CC = Custom Color specify	SCAXX = Sloped ceiling adapter 18°-45° TC = White Acrylic Top Cover	24 = 24" OAH 30 = 30" OAH 36 = 36" OAH XX" = custom length must be specified (144-24=12"- 96") (144-30=14"- 96") (144-36=16"- 96")


Notes: ¹ Fabric shade not included. Please specify fabric shade from selections provided to complete fixture order. ² Sloped ceiling adapter can accommodate up to 8-45 degree slope. Slope dimension must be provided. ³ Shade in Shade option for Fabric selections only.

ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)


Shade Number: 144-24-SHD-SIW

Series	Size	SHD	Finish		
144 = Conical Shade	24 = 24" 30 = 30" 36 = 36"	SHD = Shade Fabric	Fabric: SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige GBB = Glynn Brussels Beige	LOLA = Lola Sand NGS = Silk Glow LCK = Linen Chopstick LAT = Linen Alabaster VLW = Verona Linen White	Vinyl: ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey


DIMENSIONS



**144-24-P1S
(SINGLE STEM)**




**144-30-P1S
(SINGLE STEM)**




**144-36-P1S
(SINGLE STEM)**

OPTIONS



TOP COVER (TC)



**SLOPED CEILING
ADAPTOR (SCA)**