

Project: _____

Location: _____



Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

V-FRAME



Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately.

Frame	Lamp	Reflector Trim
502X	50W PAR20	Accepts all 4-1/4" (108mm) 500X Series trims; See Reflector Trim specification sheets.

Features

Mounting Frame: No. 20 (.032") galvanized steel. Four slots are positioned 90° apart to simplify alignment of luminaires.

Mounting Bars: 20ga. galvanized steel. Lockable on frame. Extend from 14" (356mm) to 25" (635mm). Pre-installed integral nails for secure attachment to wood joist. Attaches to T-bar ceilings without the need of accessories.

Socket Cup: 22 ga. galvanized steel. Easily snaps onto housing.

Socket: Porcelain medium base; nickel plated screw shell. Pre-wired with 18 ga. SEW leads to junction box.

Junction Box: 4" (102mm) x 3" (76mm) x 2" (51mm) 18ga. galvanized steel. CSA certified for maximum of 8 No.12ga. 90°C through branch circuit Pry-out knock-outs accept BX cable. Easy access from both sides with snap on covers.

Thermal Protector: Meets CSA/UL requirements. Insulation, if used, must be kept 3" (76mm) away from luminaire sides and junction box.

Markings

cCSAus Certified

Rated for Damp or Wet locations depending on trim used.

