


Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_



### Ordering Guide

Example: BU3 A LED13 NF W

<b>Product Code</b>	BU3	120V LED Line Voltage Composite Bullyte
<b>Finish</b>	A H G	Black Bronze Verde
<b>Source/Lumens</b>	LED13	13W LED *2
<b>Optics</b>	NF	Narrow Flood
<b>CCT</b>	W	Warm

\*1 Lamp will be shipped with fixture, but not installed. Lamp not sold separately.  
 \*2 13W LED only available in (W) warm CCT and (NF) narrow flood optics.

### Specifications

#### HOUSING:

Fully rotatable shroud, gasketed, ULTEM® High Performance Polymer composite. One-piece injection molded ULTEM® High Performance Polymer composite. Fully-adjustable swivel arm with vibration-proof locking teeth. Gasketing is silicone. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

#### FINISH:

Composite is textured, pressure formed, molded-in-color.

#### OPTICAL ASSEMBLY:

Clear tempered glass affixed at 10° angle for natural cleaning.

#### LAMPING:

13W lamp with 25° beam spread. 25,000 hours life. Color temperature (CCT): warm white (2,700K nominal). No Mercury.

#### ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

#### WARRANTY:

Ten-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

**Width:** 5 5/16" (135mm)      **Length:** 9 1/2" (241mm)      **Max. Weight:** 2.35 lb.

