



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

| Reflector Trim | Frame-In Kit — See Individual Frame-In Kit Specification Sheets |                  |            |         |
|----------------|---|------------------|------------|---------|
| 1190           | Incandescent  |                  |            |         |
|                | Frame-In Kit  | Ceiling Type     | Lamping    | Height  |
|                | 1102P1  | Non-IC           | 120W PAR38 | 6 1/2"  |
|                | 1103R   | Non-IC Remodeler |            | 6 1/2"  |
|                | 1100IC  | IC               | 90W PAR38  | 7 5/16" |
|                | 1100AICM  | AirSeal® IC      |            | 7 5/16" |
|                | 1100DICM  | Deep IC          | 75W PAR38  | 9 1/4"  |
|                | 1100DAICM   | Deep AirSeal® IC |            | 9 1/4"  |
|                | 1104ICX/N   | AirSeal® IC      | 60W PAR38  | 7 1/4"  |
|                | 1104IC/N  | AirSeal® IC      | 45W PAR38  | 7 1/2"  |
|                | 1104ICR   | IC Remodeler     |            | 7 1/2"  |
|                | 1104IC/N  | Non-IC           | 100W PAR38 | 7 1/2"  |
|                | 1104ICR   | Non-IC Remodeler |            | 7 1/2"  |

# 1190 Lytecaster Reflector 6 3/4"

## Flush Glass Wet Location Trim

### Features

1. **Housing:** Hydroformed aluminum, .040 thk. min. Non-yellowing, gloss white powder coat finish for permanent reflectivity and surface protection.
2. **Trim Flange:** Frosted clear polycarbonate flange ring. Pull down and release for toolless relamping.
3. **Frame-In Kit:** (1102P1 standard frame shown) Other frames noted. See Frame-In Kit specification sheets for more details.
4. **Glass:** Pressed borosilicate glass textured diffuser. Smooth surface on exposed side for wipe down cleaning. Meets NEC® requirements for spas and hot tubs. May be installed less than 7' 6" above max water surface height.

### Labels

UL (Suitable for Wet Locations - Covered Ceilings only), I.B.E.W.

NEC® is a registered trademark of the National Fire Protection Association.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.