


# Panel RC006

## Available wattage:




## Product features:

- Aluminium extruded with Polystyrene optic material
- White housing
- Office compliant (UGR19) versions available



Power (W)	36W	36W (UGR19)	36W	50W
Lumens	3,200 lm	3,200 lm	3,200 lm	6,000 lm
CCT (K)	4000 K	4000 K	4000 K	4000 K
Size	600 × 600 mm	600 × 600 mm	1200 × 300 mm	1200 × 600 mm
Order code	911401858585	911401858685	911401858785	911401858885



IP20



35,000 hrs (L70)



3 years warranty



IK02



Push-in connector

Power	36W	36W	50W
A (mm)	595	295	595
B (mm)	595	1,195	1,195
C (mm)	60	60	64