

Floodlight BVP009

Available wattage:




Product features:

- Robust PDC aluminium housing
- Glass diffuser
- Full IP65 construction including sensor
- PIR sensor option available
- 0.75m fly-wire cable as standard



Power (W)	10W	10W PIR	20W	20W PIR	30W	30W PIR
Lumens	850 lm	850 lm	1,700 lm	1,700 lm	2,550 lm	2,550 lm
CCT (K)	4000 K	4000 K	4000 K	4000 K	4000 K	4000 K
Beam angle	Symmetrical wide	Symmetrical wide	Symmetrical wide	Symmetrical wide	Symmetrical wide	Symmetrical wide
Order code	911401854485	911401854585	911401854685	911401854785	911401854885	911401854985

Power (W)	50W	50W PIR	70W	100W	150W	200W
Lumens	4,250 lm	4,250 lm	5,950 lm	8,500 lm	12,750 lm	17,000 lm
CCT (K)	4000 K	4000 K	4000 K	4000 K	4000 K	4000 K
Beam angle	Symmetrical wide	Symmetrical wide	Symmetrical wide	Symmetrical wide	Symmetrical wide	Symmetrical wide
Order code	911401855085	911401855185	911401858185	911401858285	911401858385	911401858485



IP65



35,000 hrs (L65)



3 years warranty



IK06



Operating temp -40° to + 50°



750mm cable length

Power	10W	10W PIR	20W	20W PIR	30W	30W PIR	50W	50W PIR	70W	100W	150W	200W
A (mm)	107	107	140	140	185	185	223	223	276	324	385	452
B (mm)	102	137	125	153	161	183	183	210	217	256	298	352
C (mm)	28	58	29	54	28	56	31	57	31	38	41	45