



Emergency options for ModuLyte, LyteProfile, and Calculite commercial downlighting families with integral or remote mounted test switch.

### Calculite LED compatibility

Calculite LED gen 3 round & square New construction (N) frames only	Nominal EM lumens	Ceiling mount with EM test button	Reflector trim mount with EM test button
3"	430-660lm	Standard	Available (round DL only)
4"	680-760lm	Standard	Available (DL and WW only)
6" & 7"	680-760lm	Standard	Available (DL and WW only)

### LyteProfile LED compatibility

LyteProfile LED round New construction (N) frames only	Nominal EM lumens	Ceiling mount with EM test button	Reflector trim mount with EM test button
3"	430-660lm	Standard	Available (round DL only)
4"	690lm	Standard	Available (DL only)
6"	700lm	Standard	Available (DL only)

### Modulyte LED compatibility

Modulyte LED round New construction (N) frames only	Nominal EM lumens	Ceiling mount with EM test button	Reflector trim mount with EM test button
4"	660lm	LCEM6 Field Installed Accy or EM6R factory option	EM6I factory option
6"	720lm		EM6I factory option
8"	720lm		EM6I factory option

IEM6 Option Codes		Switch Orientation by Shape		
Family	Aperture/Type	Remote	Integral	Excluded Integral Styles
Calculite	3" DL/LW/AA	●■	●	LW, AA
	4" DL/WW	●■	●■	LW, AA
	6" DL/WW	●■	●■	LW
	7" DL/WW	●	●	LW

IEM6 Option Codes		Switch Orientation by Shape		
Family	Aperture/Type	Remote	Integral	Excluded Integral Styles
LyteProfile	3" DL/LW/AA	●■	●	LW, AA
	4" DL/LW	●■	●■	LW
	6" DL/LW	●■	●■	LW
EasyLyte	4" DL	●	---	---
	6" DL	●	---	---
Modulyte	4" DL	●	---	Cylinders
	6" DL	●	---	Cylinders

### Features

**Battery pack:** Bodine BSL06 battery pack featuring self-test and self-diagnostic functionality provides 90 minutes of lighting when AC power fails. Meets National Electrical and Life Safety Codes. Accessible from below with attachment to the back side of the new construction frame junction box. Compatible with 120/277V.

To estimate lumen output in emergency mode, multiply emergency pack wattage by luminaire configuration efficacy, then by 1.1.

### Test switch/charge light

**Trim Mount:** Can be installed integral to trim when ordered with IEM6 option code

**Examples:**

Calculite (trim): C4RDLCC1EM6

LyteProfile: P4RDL25935WCCZ10U1EM6

ModuLyte: M4RDL259CSWCDZ10UEM6I

**Remote Mount:** Order CAEM6TSCP mounting plate accessory. See line art on page 2 for CAEMTSCP for dimensions.

**Mounting:** Tool-less attachment to back side of new construction frame junction box.

### Labels and Listings

cULus listed for damp locations only. Not approved for Chicago plenum applications.

### Warranty



5 year limited warranty

Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty on complete luminaire systems.

# LED-EM Calculite, LyteProfile, & EasyLyte Emergency Battery Pack


## Accessories

**CAEM6:** For use with Calculite and LyteProfile engines with new construction (N) frames only. Field install EM6 kit with Bodine BSL06 6W battery pack with self-test/self-diagnostic. Includes EM pack mounted on cover plate for attachment to back side of junction box. Includes CAEM6TSCP rectangular plate for remote mounting test switch. To mount test switch to trim for new construction frame, order Calculite trim or LyteProfile engine with IEM6 option code.




**LCEM6:** For use with Calculite and LyteProfile Flex retrofit engines. Bodine BSL06 6" battery pack provided on a floating junction box ideally used in remodel or retrofit applications. Refer to [LCEM6 specification sheet](#) for more details.

**CAEM6TSCP:** Ceiling cover plate for remote mounted EM6 test switch. 1/2" (25mm) hole, 4 3/8" (109mm) x 2 3/4" (69mm) rectangular. Includes two mounting screws. White finish.



**MLEM6:** For use with ModuLytic engines. Bodine BSL06 6" battery pack provided on a floating junction box ideally used in remodel or retrofit applications. Refer to [ModuLytic downlight specification sheet](#) for more details.



**LCEM6**




**MLEM6**




# LED-EM Calculite, LyteProfile, & EasyLyte Emergency Battery Pack


## 3RN/4RN frame dimensions



## 3SN/4SN/6RN frame dimensions






## 6SN/7RN frame dimensions



### CAEM6TSCP Cover Plate Accessory

Purchased separately for remote test switch

Included with CAEM6 field installed EM pack



### Round Apertures

3" - 1 1/8" (46mm)  
4" - 2 3/8" (60mm)  
6" - 3 3/8" (85mm)  
7" - 1 1/8" (105mm)

### Square Apertures

4" - 2 1/4" (55mm)  
6" - 2 5/8" (66mm)

\* Emergency battery pack shown with EM6 option on new construction non-IC frame.

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

**GENLYTE**  
**SOLUTIONS**

a  Signify business

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.