

Day-Brite

CFI

by Signify

Industrial

Twist-lock power hook

Accessories

Project: _____

Location: _____


Cat.No: _____

Type: _____

Lamps: _____ Qty: _____


Notes: _____

Ordering Matrix



Product Features

- Die cast aluminum.
- Provisions for pendant and through feed 3/4" NPS mounting or surface mounting using two 1/4" bolts.
- UL Listed load break device.
- Receptacle provides a "positive ground".
- Large access opening with cover.
- Standard NEMA receptacle
 - L5-15R for 120 volts
 - L6-15R for 280, 240 volts
 - L7-15R for 277 volts
 - L24-20R for 347 volts
 - L8-20R for 480 volts



PH Twist-lock power hook

Dimensions

