




1090/1003R
Lytefning™ Non-IC
Remodeler Ring



1090/1004IC
Lytefning™ Convertible
Non-IC only



1090/1004ICX
Lytefning™ AirSeal®
Insulated Ceiling



Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Reflector Trim	Frame-In Kit — See Individual Frame-In Kit Specification Sheets			
1090 Flush Glass Trim Wet Location	Incandescent			
	Frame-In Kit	Ceiling Type	Lamping	Height
	1002P1 1003R	Non-IC Non-IC Remodeler	75W PAR30L	5 1/4" 5 1/4"
	1000IC 1000AICM 1004ICX/N	IC AirSeal® IC AirSeal® IC	60W PAR30S	7 5/16" 7 5/16" 7 1/4"
	1004IC/N 1004ICR	Non-IC Non-IC Remodeler	75W PAR30S	7 1/2" 7 1/2"

Features

- Housing:** Hydroformed aluminum, .040 thick. min. Non-yellowing, gloss white powder coat finish for permanent reflectivity and surface protection.
- Trim Flange:** Frosted clear polycarbonate flange ring. Pull down and release for toolless relamping.

- Frame-In Kit:** (1002P1 standard frame shown) Other frames noted. See Frame-In Kit specification sheets for more details.
- Glass:** Pressed borosilicate glass textured diffuser. Smooth surface on exposed side for wipe down cleaning. Meets NEC® requirements for spas and hot tubs. May be installed less than 7' 6" above max water surface height.

Labels

UL (Suitable for Wet Locations - Covered Ceilings only), I.B.E.W.

NEC® is a registered trademark of the National Fire Protection Association.

