



Program

QuickShip

10-day



**We couldn't increase
the speed of light,
but we found a way
to get it to you faster.**

As the complexity of your projects has skyrocketed, fast delivery of your lighting has become increasingly important.

The Ledalite 10-day QuickShip program includes all of our high performance and award-winning LED linear, recessed, surface and slot luminaire families.

Please note: Due to continuing product improvements, Ledalite reserves the right to change product specifications without notice.

quickship

Questions?
Call your Ledalite sales rep.

	ModiFly (MF)	FloatPlane (24)	BoldPlay (78)	Sync (74)	Verge (76)
Product Family					
Mounting	Suspended	Suspended	Suspended	Suspended	Suspended
Color Temp	3000K, 3500K and 4000K				
Lumen Package	All lumen packages available (varies by product)				
Distribution	Direct/Indirect				
Wiring Configurations*	1cct Dimming (0-10V) · Available Options: Aux. Wiring or Battery Pack				
End Caps (Default)	Standard	Sculpted		Flat	Sculpted
Module Lengths	All available module lengths, standalone or continuous rows (varies by product)				

	Jump (12)	TruGroove (29)	Sona (77)	MicroSquare (22)	Chopstick (75)
Product Family					
Mounting	Suspended/ Surface	Suspended/ Surface	Suspended	Suspended/ Surface	Suspended
Color Temp	3000K, 3500K and 4000K				
Lumen Package	All lumen packages available (varies by product)				
Distribution	Direct	Direct, Indirect, Direct/Indirect			Semi-Indirect
Wiring Configurations*	1cct Dimming (0-10V) · Available Options: Aux. Wiring or Battery Pack				
End Caps (Default)	Sculpted			Solid Cube	Flat
Module Lengths	All available module lengths, standalone or continuous rows (varies by product)				

Exclusions:

- ModiFly and TruGroove: no patterns or rows that require drawings
- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- Prior **Hold for Release** or **Do Not Ship Before** orders
- All non-standard, 3rd party drivers and components
- No Battery Pack is available for 347V

*** Note:** Not all wiring configurations are available with all LED light source options. White, titanium and black finishes available. All standard optics and downlight kits available.

Questions? Call your Ledalite sales rep.



Recessed LED

Limit of 100 units per release

	ArcForm (36)	VersaForm (41)	SilkSpace (42) performance & definition
Product Family			
Size	2'x2', 1'x4'	2'x2', 2'x4', 1'x4'	2'x2', 2'x4', 1'x4'
Color Temp	3000K, 3500K and 4000K		3000K, 3500K and 4000K (all versions) 2700K & 5000K (definition only)
Lumen Package	All lumen packages available (varies by product)		
Wiring Configurations*	1cct Dimming (0-10V) • Available Option: Battery Pack		
Ceiling Type			
Standard T-Grid	YES		
Slot/Tegular T-Grid	YES		Fixture will sit 5/16" above bottom of T-Bar.
Drywall Kits	YES		
Options	Pre-installed 6' Flex Whips		

	PureFX (94)	Vectra (97)	Shine (33)
Product Family			
Size	2'x2', 1'x4'	2'x2', 1'x4'	2'x2', 2'x4', 1'x4'
Color Temp	3000K, 3500K and 4000K		2700K, 3000K, 3500K, 4000K & 5000K
Lumen Package	All lumen packages available (varies by product)		
Wiring Configurations*	1cct Dimming (0-10V) - Available Option: Battery Pack		
Ceiling Type			
Standard T-Grid	YES		
Slot/Tegular T-Grid	YES		Fixture will sit 5/16" above bottom of T-Bar.
Drywall Kits	YES		
Options	Pre-installed 6' Flex Whips		

Exclusions:

- All non-standard, 3rd party drivers and components
- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- No Battery Pack is available for 347V
- Prior **Hold for Release** or **Do Not Ship Before** orders
- Surface mount versions
- Chicago housings
- Air Return housings

***Note:** Not all wiring configurations are available with all LED light source options. **Questions? Contact your Ledalite sales rep.**

	TruGroove Recessed (39)	TruGroove Recessed Micro (23)	TruGroove Perimeter (49)	TruGroove Cove (TC)
Product Family				
Mounting	Linear Recessed	Linear Recessed	Perimeter	Cove
Color Temp	3000K, 3500K and 4000K			
Lumen Package	All lumen packages available (varies by product)			
Distribution	Symmetric/Asymmetric		Ambient/Graze	Focus/Fill
Module Lengths	Row lengths from 2' to 20' in 2' increments			All lengths in 6" increments, starting at 2'
Wiring Configurations*	1cct Dimming (0-10V) Available Options: Aux. Wiring or Battery Pack			

Exclusions:

- Prior **Hold for Release** or **Do Not Ship Before** orders
- No Battery Pack is available for 347V
- All non-standard, 3rd party drivers and components
- TruGroove Recessed Micro (23) not available as a 2ft asymmetric length
- No patterns or rows that require drawings
- TruGroove Cove (TC) 6000lm/4ft not available with 90CRI options.
- Thru-wiring for additional circuits
- Connected options (SpaceWise, Interact Pro, Tunable White, PoE)
- Chicago housings

*Note: Not all wiring configurations are available with all LED light source options. Questions? **Contact your Ledalite sales rep.**

Information current from January, 2020 - Check ledalite.com for ongoing updates.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

