





User manual




Model	Product Description	Power(W)	CRI(Ra)	CCT(K)	Total Lumen (lm)	Useful lumen (lm)	Energy efficiency class of light source	Beam angle	Dimmension AxB,C(mm)	Cut-Out D(mm)	Weight (kg)
9290047210	Cilantro Step Dim 070 5W 27K VWH	5	80	2700	500	450	F	36°	φ90*36	φ68-75	0.08
9290047211	Cilantro Step Dim 070 5W 40K VWH			4000	550	495					
9290047212	Cilantro Step Dim 070 5W 27K BL			2700	500	450					
9290047213	Cilantro Step Dim 070 5W 40K BL			4000	550	495					

Dimensions




Size:210x297mm


Installation



Inrush current



Step dimming operation



WARNING:

- 01 Please read this manual before you start to install the luminaire.
- 02 The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations of the national requirements.
- 03 Switch OFF the power supply before the installation or maintenance to avoid electrical shock.
- 04 The luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, Phthalates, etc., are present.

ATTENTION: In B manual, you will find all the explanations with numeric reference to the icons respectively in front of these safety instructions.



3241 662 45371
©2024 Signify Holding


Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. and are used under license.