






PHILIPS



Cilantro Recessed Spotlight

User manual




Model	Product Description	Power(W)	CRI(Ra)	CCT(K)	Total Lumen (lm)	Useful lumen (lm)	Energy efficiency class of light source	Beam angle	Dimension AxB,C(mm)	Cut-Out D(mm)	Weight (kg)
9290049365	Cilantro Step Dim 070 5W 27K WH M	5	80	2700	500	450	F	36°	φ90*36	φ68-75	0.08
9290049366	Cilantro Step Dim 070 5W 40K WH M			4000	550	495					
9290049367	Cilantro Step Dim 070 5W 27K BL M			2700	500	450					
9290049368	Cilantro Step Dim 070 5W 40K BL M			4000	550	495					


Dimensions




Installation



Inrush current



Step dimming operation



When the luminaire is turned off, the state before turning off will be memorized in system.
* If the luminaire is turned off for more than 3 seconds and then turned on again, the luminaire will be set to the state before turning off.
** To switch the light states, only need to turn off the luminaire for 1 to 3 seconds and then turn it on.
*** The reset operation will synchronize all the lights to the initial state, in case there is out of sync in brightness between the luminaires.

WARNING:

- 01 Please read this manual before you start to install the luminaire.
- 02 The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations of the national requirements.
- 03 Switch OFF the power supply before the installation or maintenance to avoid electrical shock.
- 04 The luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, Phthalates, etc., are present.

ATTENTION: In B manual, you will find all the explanations with numeric reference to the icons respectively in front of these safety instructions.



3241 662 45372
© 2026 Signify Holding
Signify