




Complete fixture consists of the Housing, Trim and Frame-in Kit. Select each separately.

Reflector Trim		Frame-in Kit (Low Voltage)		Lamp	Voltage
346WWHX	White paint flange	Remodeler Non-IC	300MRSPX	37W MR16 IR	120V
346WSTX	Brushed Steel Flange	Remodeler Non-IC	3401MREX	37W MR16 IR	120V
		Frame Non-IC	302MRLX	50W MR16 / 37W MR16 IR	120V
		Frame Non-IC	302MRSPX	50W MR16 / 37W MR16 IR	120V
		Frame Non-IC	302MREX	50W MR16 / 37W MR16 IR	120V
		Frame IC	302MRIC9SPX	37W MR16 IR	120V
		Lytening Frame AirSeal®	302MRAICSPX	35W MR16	120V
		Lytening Frame AirSeal®	302MRAICEX	35W MR16	120V
		Frame-in Kit (HID)		Lamp	Voltage
		Remodeler Non-IC	302MH39MRE1	39W MR16 CMH	120V

Features

Housing: 25 ga steel. Black painted finish.

Residence Mounting Clips: Factory-installed; zinc plated spring steel; free-hand installation.

Flange: Die-cast aluminum 0.060" (1.5mm) thick.

Reflector : Steel 24ga painted white, for a uniform light diffusion.

Mounting Clips (2): 24 ga. spring steel, zinc plated. Provides easy snap-in / snap-out action.

Lamp guard: 2" (51mm) dia. borosilicate glass.

(Not required for CMH lamps)

Lens Support: Die-cast aluminum 0.125" (3.2mm) thick. Painted black.

Asymmetric Lens: Soda-lime temper glass frosted on one side.

Accessories

2" (51mm) dia. Glass Colour Filters: See ADF2 Specification Sheet.

2" (51mm) dia. Specialized Filters: See AF2 Specification Sheet.


Frame-in Kit

See Frame-In Kit specification sheets for more details.

Marking

cCSAus Certified, suitable for damp locations,

Job Information	Type:
Job Name:	
Cat. No.:	
Lamp(s):	
Notes:	



Le luminaire complet comprend le Boîtier, la Garniture et le Cadre de montage : Choisir chacun séparément.

Garniture du Réflecteur	Cadre de montage (Basse tension)	Lampe	Voltage
346WWHX Garniture peinte blanche	Rénovation Non-IC	300MRSPX	37W MR16 IR
346WSTX Bordure acier brossée	Rénovation Non-IC	3401MREX	37W MR16 IR
	Cadre Non-IC	302MRLX	50W MR16 / 37W MR16 IR
	Cadre Non-IC	302MRSPX	50W MR16 / 37W MR16 IR
	Cadre Non-IC	302MREX	50W MR16 / 37W MR16 IR
	Cadre IC	302MRIC9SPX	37W MR16 IR
	Lytening Cadre AirSeal®	302MRAICSPX	35W MR16
	Lytening Cadre AirSeal®	302MRAICEX	35W MR16
Cadre de montage (DHI)		Lampe	Voltage
	Rénovation Non-IC	302MH39MRE1	39W MR16 CMH

Caractéristiques

Boîtier : en acier de calibre 25. Fini peinturé noir.

Attaches de montage Résidence : pré-assemblé en usine. Ressort en acier plaqué zinc. Le luminaire tient en place dans le plafond sans besoin de le retenir pendant l'ajustement.

Bordure : en aluminium moulé sous pression de 0.060po. (1.5mm) d'épaisseur.

Réflecteur : acier de calibre 24 peinturé blanc, pour une diffusion uniforme de l'éclairage.

Attaches de montage (2) : ressort en acier inoxydable de calibre 24. Facile à enlever et à remettre en place.

Lentille de protection : verre de 2 po (51mm) de diamètre en borosilicate. (Non requise pour les lampes CHM)

Support de lentille : aluminium moulé sous pression, .0125 po d'épaisseur ; peinturé noir.

Lentille asymétrique : verre en sodocalcique trempé et givré d'un côté.

Accessoires

Filtres colorés en verre de 2 po (51mm) dia. : voir la feuille de spécification ADF2.

Filtres spécialisées de 2 po (51mm) dia. : voir la feuille de spécification AF2.

Cadre de Montage

Pour les caractéristiques des cadres de montage, voir les fiches techniques appropriées.

Marquage

Certifié cCSAus ; convient aux endroits humides.

Information Projet	Type:
Nom Projet:	
No. Cat.:	
Lampe(s):	
Notes:	