

Project:

Location:

Cat.No:

Type:


Lamps:Qty:

Notes:

Ordering Guide

Example: 303- 8 ABS B B D

Product Code	303-	Anchor Base Post
Height(s)	8 10 12 14 16	(8 ft.) (10 ft.) (12 ft.) (14 ft.) (16 ft.)
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Photoeye (Optional)	B C	120V 208V - 277V
Outlet Location (Optional)	B T	4" from Top of Base 12" from Top of Pole
Outlet Options (Optional)	D G	Standard Duplex GFI Duplex



Specifications

**OUTLET:**  
GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# 303- Anchor base post

## Pole

### Specifications

- CONSTRUCTION:**  
Cast aluminum anchor base. Cast aluminum removable access door. Round fluted post welded to base. Tenon secured to post top. Cast aluminum upper base welded to base & post.
- FINISH:**  
Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.
- WARRANTY:**  
Three-year limited warranty.
- Tenon/Top:**  
3" O.D.
- Bolt Circle:**  
7" dia.
- Anchor Rods:**  
(4) 3/4" dia. x 15" long zinc plated steel
- Base Dimensions:**  
17" dia. x 18 3/4"
- Shaft:**  
4" Round Fluted
- Wall Thickness:**  
.125"
- Height:**  
8', 10', 12', 14', 16'

### Pole EPA Values

Windspeed(mph)	Height				
	8'	10'	12'	14'	16'
80	25.4900	16.9400	12.3200	9.3500	7.2300
110	14.7600	9.5800	6.7100	4.8200	3.4400
130	10.1900	7.3100	5.2400	3.4300	2.0200

