

Shaper

DESCRIPTION

674 Luminous Wall Sconce features horizontal trim bars with a vertical fin detail and is ADA compliant.

Catalog #		Type	
Project			
Comments		Date	
Prepared by			

SPECIFICATION FEATURES

Material

Painted, solid aluminum with a 1/8" matte white acrylic diffuser panel. 674-W features an open top and bottom with a regressed aluminum perf shield for interior applications. The 674-WP is rated for exterior applications.

Finishes

ALP (Aluminum Paint)
MW (Matte White)
MB (Matte Black)
GRM (Graphite Metallic)
DP (Dark Platinum)
BM (Bronze Metallic)
CC (Custom Color – Specify)

For Custom Color contact factory for quotation.

LED

31" L3:2000 nominal lumens at max 19W
43" L4:3000 nominal lumens at max 29W
55" L5:4000 nominal lumens at max 38W

Driver

LED system coupled with electronic driver to deliver optimal performance. Electronic drivers are available for 120-277V applications. A 0-10V dimming control is available (Standard) on all models.

Installation


Supplied with a universal circular strap for a standard 4" J-box or plaster ring.

Options

RBP-Remote Emergency Battery Pack (5' Max Distance).


Compliance

674-W is U.L. and C.U.L approved for indoor and damp location. ADA compliant. 674-WP is U.L. and C.U.L listed for wet location.



674-W Series 674-WP Series

DIMENSIONS



31"

- Lumen Output Source Lumens: L3:2000 nominal lumens
- Wattage: 20W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V
- Warranty: Warranty: 5 year limited

43"

- Lumen Output Source Lumens: L4:3000 nominal lumens
- Wattage: 29W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V
- Warranty: Warranty: 5 year limited

55"

- Lumen Output Source Lumens: L5:4000 nominal lumens
- Wattage: 38W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V
- Warranty: Warranty: 5 year limited

ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Sample Number: 674-55-W-L5/827-UNV-MW-RBP

Series	Size	Mounting Type	LED Lamp			LED Voltage	Finish	Options
			31"	43"	55"			
674 = Luminous Wall Sconce	31 = 31"	W = Interior Wall				UNV = (120-277V)	ALP = Aluminum Paint MW =Matte White MB =Matte Black DP =Dark Platinum GRM =Graphite Metallic BM =Bronze Metallic CC =Custom Color - Contact factory for quotation	RBP = Remote Battery Pack (5' Max Distance)
	43 = 43"	WP = Exterior Wall	L3/827	L4/827	L5/827			
	55 = 55"		L3/830	L4/830	L5/830			
			L3/835	L4/835	L5/835			
			L3/840	L4/840	L5/840			