


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____



Ordering Guide

Example: BL616 A S7 BAB

Product Code	BL616	Aluminum Bullyte
Finish	A G H	Black Verde Bronze
Mounting	S7	Mounting Stake
Lamp	BAB	20W MR16

*1 Each product will ship with an S7
 *2 BAB Lamp is optional

Specifications

HOUSING:

1/2" NPS male threads to screw onto accessory mounting stake or junction box. Die-cast marine grade aluminum alloy. Fully rotatable shroud, gasketed, die-cast marine grade aluminum alloy. Fully-adjustable swivel arm with vibration-proof locking teeth. Fasteners are 300 series stainless steel.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

OPTICAL ASSEMBLY:

Clear tempered glass lens.

LAMPING:

50W maximum MR16 bi-pin lamp. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width:

3" (77mm)

Length:

5 1/2" (141mm)

Max. Weight:

1.04 lb

