

Shaper

DESCRIPTION

The 146 series is a decorative pendant family with a cylindrical form. This product has a tall cylindrical shade with a variety of options. The integral LED light engine is available in 2700K, 3000K, 3500K, 4000K color temperatures that evenly illuminates the shades and bottom lens with 83+ CRI. The stem, canopy, and finial finishes are available in many painted options. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Shades come in 3 standard sizes, 11 standard fabrics, 4 printed woods, and 3 vinyl materials. This series also comes with the option for a 3 or 4 pendant cluster.

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover available (TC).

5" diameter canopy with self aligning swivel. Stem is 1/2" aluminum tubing with threaded rod. Air craft cable option is 3/64" cable. Slope adapter option available (SCA-XX - 18°- 45°, but slope dimension must be provided).

28" H x 10" Diameter

Standard Length=
40" OAH (Overall Height)

Min	Max
32" OAH	96" OAH

40" H x 10" Diameter

Standard Length=
54" OAH (Overall Height)

Min	Max
44" OAH	96" OAH

52" H x 10" Diameter

Standard Length=
64" OAH (Overall Height)

Min	Max
56" OAH	96" OAH

Stem Options	
Single Rigid Stem	-P1S
Air Craft Cable	-P1SAC
3 Stem Cluster	-3FCL
4 Stem Cluster	-4FCL

Consult factory for non standard lengths under 18" and over 96".

Painted Finishes

(canopy, stem, and finial)
ALP (Aluminum Paint)
BM (Bronze Metallic)
DP (Dark Platinum)
GRM (Graphite Metallic)
MB (Matte Black)
MW (Matte White)
CC (Custom Color – Specify)
Consult factory for custom color.

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl Shade in Shade offers 2 material selections, overlapping each other.

Fabric Shade Selections

SIW - Silk White
SIY - Silk Ivory
SWH - Shantung White
SEG - Shantung Eggshell
SBG - Shantung Beige
LAT - Linen Alabaster
LCK - Linen Chopstick
NGS - Silk Glow
GBB - Glynn Brussels Beige
LOLA - Lola Sand
VLW - Verona Linen White

Catalog #	Type
Project	
Comments	
Prepared by	
	Date

Vinyl Coated Fabric

ABR - Alabaster Vinyl
NFX - Natural Flax
GHY - Golden Honey

Printed Wood

PVDB - Varigated Bamboo
PMA - Maple
PCH - Cherry
PWA - Walnut

Note: For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended.

LEDs

LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated LED Life: 50,000 hrs.

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.



146 SERIES

Diameter: 28"

- Delivered Lumens (@3500K): 1362
- Wattage: 19W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

Diameter: 40"

- Delivered Lumens (@3500K): 4023
- Wattage: 28W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

Diameter: 52"

- Delivered Lumens (@3500K): 2948
- Wattage: 37W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Fixture Number: 146-28-P1S-L3/835-UNV-ALP-40

Shade Number: 146-28-SHD-SWH

Series ¹	Shade Height	Mounting Type	LED Lamp	LED Voltage	Finish	Options	Overall Height (OAH)
146 = Cylinder Pendant	28 = 28" 40 = 40" 52 = 52"	P1S = Single Stem P1SAC = Single Stem w/ Aircraft Cable 3FCL = 3 Stem Cluster 4FCL = 4 Stem Cluster	28" L3/827 L3/830 L3/835 L3/840 40" L4/827 L4/830 L4/835 L4/840	52" L5/827 L5/830 L5/835 L5/840	UNV (120-277)	MW = Matte White MB = Matte Black BM = Bronze Metallic DP = Dark Platinum ALP = Aluminum Paint GRM = Graphite Metallic CC = Custom Color specify	SCA = Sloped ceiling adapter ² 18'-45' TC = Matte White Acrylic Top Cover 40 = 40" OAH (28" shade height) 54 = 54" OAH (40" shade height) 64 = 64" OAH (52" shade height) XX = Custom length must be specified (146-28 = 32" - 96" 146-40 = 44" - 96" 146-52 = 56" - 96") See "Dimensions" section for Overall Height per fixture length per cluster type.

Notes: ¹ Fabric shade not included. Please specify fabric shade from selections provided to complete fixture order. ² Sloped ceiling adapter can accommodate up to 18-45 degree slope. Slope dimension must be provided.

³Shade in Shade option for Fabric selections only.


Shade Number: 146-28-SHD-SIW

Series	Size	SHD	Finish		Options	
146 = Cylinder Shade	28 = 28" 40 = 40" 52 = 52"	SHD = Shade	Fabric: ^{4,5,6} SIW = Silk White SIY = Silk Ivory SWH = Shantung White SEG = Shantung Eggshell SBG = Shantung Beige LAT = Linen Alabaster GBB = Glynn Brussels Beige	LOLA = Lola Sand LCK = Linen Chopstick NGS = Silk Glow VLW = Verona Linen White	Printed Wood: ^{4,5} PVDB = Varigated Bamboo PMA = Maple PWA = Walnut PCH = Cherry Vinyl Coated Fabric: ^{4,5} ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey	Organza Outer Shade ^{4,5,6} TRDSIS-EDT = Top Round-in Shade, Earth Dust TRDSIS-WMT = Top Round-in Shade, White Mist


Notes: ⁴ Available for 28". ⁵ Available for 40". ⁶ Available for 52".

OPTIONS





MOUNTING - SINGLE PENDANT




MOUNTING - SINGLE PENDANT - SHADE IN SHADE




DIMENSIONS - 3 CLUSTER PENDANT




DIMENSIONS - 4 CLUSTER PENDANT




146-28-4FCL
(MULTI-HEAD CYLINDER PENDNAT)



146-40-4FCL
(MULTI-HEAD CYLINDER PENDNAT)



146-52-4FCL
(MULTI-HEAD CYLINDER PENDNAT)



146-4FCL-PLAN VIEW
(FOUR FIXTURE PENDANT CLUSTER)