



Save Money



Save Time



Peace of Mind

The Metalux SLES with socket-fit light engine is a TLED striplight that provides an affordable, energy savings solution vs. traditional fluorescent lighting. Designed for retrofit and new construction, the SLES uses flip-up sockets, snap-on channel aligner and tool-less cover for faster installation time. TLEDs are available in 4' lengths with 3500K, 4000K, and 5000K CCT options. The SLES is available in 4' and 8' lengths and is ideal for retail environments with large, open ceilings.





















# SLES

## Socket-Fit Light Engine Striplight

# Metalux



 Save Money
  Save Time
  Peace of Mind

Category	Feature	Benefit	Result
Construction	Flip-up sockets, snap-in channel connector and cover	Reduce installation time	  
	Replaceable TLED lamps	Lower maintenance costs; no fixture replacement necessary	  
	End plate converts to snap-on channel aligner for continuous row mounting	Fast, In-Row alignment	  
Performance	DLC qualified and up to 167 lpw	Maximize energy savings and rebates	  
	UL listed for damp locations	Can be used in wet locations, both indoors and outdoors	  
	5-year limited warranty	Guaranteed performance	  

### Ordering Information/Performance

Catalog	Product Description	Lumen Output, 83 CRI			Efficacy			Wattage
		3500K	4000K	5000K	3500K	4000K	5000K	120-277V
4SLES-1-T8-1G-B8XX-U	4ft 1-lamp T8 SLES strip, 120-277V, 9.9W CorePro Type B TLED included, Glass TLED	1706	1760	1760	172	178	178	9.9
4SLES-2-T8-1G-B8XX-U	4ft 2-lamp T8 SLES strip, 120-277V, 9.9W CorePro Type B TLED included, Glass TLED	3323	3427	3427	168	173	173	19.8
4SLES-1-T8-2G-B8XX-U	4ft 1-lamp T8 SLES strip, 120-277V, 12W CorePro Type B TLED included, Glass TLED	1813	1920	1920	151	160	160	12
4SLES-2-T8-2G-B8XX-U	4ft 2-lamp T8 SLES strip, 120-277V, 12W CorePro Type B TLED included, Glass TLED	3531	3739	3739	147	156	156	24
4SLES-1-T8-3G-B8XX-U	4ft 1-lamp T8 SLES strip, 120-277V, 14.5W CorePro Type B TLED included, Glass TLED	2133	2240	2240	147	154	154	14.5
4SLES-2-T8-3G-B8XX-U	4ft 2-lamp T8 SLES strip, 120-277V, 14.5W CorePro Type B TLED included, Glass TLED	4154	4362	4362	143	150	150	29
8TSLES-1-T8-1G-B8XX-U	8ft Tandem 1-lamp T8 SLES strip, 120-277V, (2) 9.9W CorePro Type B TLED included, Glass TLED	3413	3519	3519	172	178	178	19.8
8TSLES-2-T8-1G-B8XX-U	8ft Tandem 2-lamp T8 SLES strip, 120-277V, (4) 9.9W CorePro Type B TLED included, Glass TLED	6647	6855	6855	168	173	173	39.6
8TSLES-1-T8-2G-B8XX-U	8ft Tandem 1-lamp T8 SLES strip, 120-277V, (2) 12W CorePro Type B TLED included, Glass TLED	3626	3839	3839	151	160	160	24
8TSLES-2-T8-2G-B8XX-U	8ft Tandem 2-lamp T8 SLES strip, 120-277V, (4) 12W CorePro Type B TLED included, Glass TLED	7062	7478	7478	147	156	156	48
8TSLES-1-T8-3G-B8XX-U	8ft Tandem 1-lamp T8 SLES strip, 120-277V, (2) 14.5W CorePro Type B TLED included, Glass TLED	4266	4479	4479	147	154	154	29
8TSLES-2-T8-3G-B8XX-U	8ft Tandem 2-lamp T8 SLES strip, 120-277V, (4) 14.5W CorePro Type B TLED included, Glass TLED	8309	8724	8724	143	150	150	58

Note: Lamps shipped separately from fixture.



**Cooper Lighting Solutions**  
 1121 Highway 74 South  
 Peachtree City, GA 30269  
 P: 770-486-4800  
[www.cooperlighting.com](http://www.cooperlighting.com)

**Canada Sales**  
 5925 McLaughlin Road  
 Mississauga, Ontario L5R 1B8  
 P: 905-501-3000  
 F: 905-501-3172

© 2021 Cooper Lighting Solutions  
 All Rights Reserved  
 Printed in USA  
 Publication No. SA519095EN  
 July 9, 2021 3:28 PM