



Combines elegant performance with sheer brilliance. **Lumec's Contemporary Lantern Series** brings the lantern style of design into the 21st century. This series combines elegance and performance with sheer brilliance. Without question, the **Contemporary Lantern Series** offers a discerning quality that adds a timeless finishing touch to the most beautiful installations.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering guide

example: L80-SE-SF8050MHR5120SF80HSCRAAPR4-LBC3-BE2TX

| Luminaire | Lamp | Optical System | Voltage | Adaptor | Options | Mounting & Configuration | Pole | Finish |
|----------------------|----------------------|---|-----------------|-------------|---|---|---|---|
| L80-SE-SF80 | 50MH medium | RR Optics | DH1 | SF80 | FN Decorative finial (see below) | CRA | APR4-LBC3 | BE2TX Midnight Blue Textured |
| L81-RACE-SF80 | 70MH medium | RR5 Symmetrical | 120 120V | SF0 | | CRC | APR4-LBC3 | BE6TX Ocean Blue Textured |
| L82-RACE-SF80 | 100MH medium | RR3 Asymmetrical | 208 208V | SF5 | HS House shield (with SE only) | CRD | APR4-LBC3 | BE8TX Royal Blue Textured |
| | 150MH medium | RR3MD Asymmetrical with medium deflector | 240 240V | SF70 | | CRF | APR4-LBC3 | BG2TX Sandstone Gold Textured |
| | 200MH mogul | SE Optics | 277 277V | SF72 | | <i>Consult the eCatalog for details and the complete line of mountings.</i> | <i>Consult the eCatalog for details and the complete line of mountings.</i> | BKTX Black Textured |
| | 250PSMH mogul | SE5 Symmetrical | 347 347V | SF73 | | | | BRTX Bronze Textured |
| | 35HPS mogul | SE3 Asymmetrical | 480 480V | | | | | GN4TX Blue Green Textured |
| | 50HPS mogul | > House shield available in option (HS). | | | | | | GN6TX Forest Green Textured |
| | 70HPS mogul | RACE Optics | | | | | | GN8TX Dark Forest Green Textured |
| | 100HPS mogul | RACE5 Symmetrical | | | | | | GNTX Green Textured |
| | 150HPS mogul | RACE3 Asymmetrical | | | | | | GR Gray sandtex |
| | 200HPS mogul | RACE3D Asymmetrical with deflector | | | | | | GY3TX Medium Grey Textured |
| | 250HPS mogul | | | | | | | RD2TX Burgundy Textured |
| | | | | | | | | RD4TX Scarlet Textured |
| | | | | | | | | WHTX White Textured |
| | | | | | | | | NP Natural Alum. |
| | | | | | | | | TG Hammer-tone Gold |
| | | | | | | | | TS Hammer-tone Silver |


1. Multi-top ballast also available.

L80-L81-L82 Contemporary Lantern

Post Top

Luminaires


L80-SE-SF80



EPA: 1.32 sq. ft.

Weight: 45 lbs (20.4 kg)


L81-RACE-SF80



EPA: 1.32 sq. ft.

Weight: 44 lbs (20.0 kg)

L82-RACE-SF80



EPA: 1.32 sq. ft.

Weight: 45 lbs (20.4 kg)

Benefits

- Constructed from top-quality materials, the Contemporary Lantern Series maintains excellent performance in even the most demanding environments.
- Prismatic RR optics, SE cut-off reflectors, and the RACE optical system, are available to meet a range of lighting applications.
- Polycarbonate globe has satin-finish to gently obscure the source without compromising photometry.
- Toolfree access to lamp and electrical components for ease of maintenance.
- Unique styling merges traditional and contemporary design.

Lamp/HID

| Wattage | Race | RR | SE |
|----------------|------|----|----|
| 50MH, medium | ■ | ■ | ■ |
| 70MH, medium | ■ | ■ | ■ |
| 100MH, medium | ■ | ■ | ■ |
| 150MH, medium | ■ | ■ | ■ |
| 200MH, mogul | RB | RB | RB |
| 250PSMH, mogul | RB | RB | RB |
| 35HPS, mogul | ■ | ■ | ■ |
| 50HPS, mogul | ■ | ■ | ■ |
| 70HPS, mogul | ■ | ■ | ■ |
| 100HPS, mogul | ■ | ■ | ■ |
| 150HPS, mogul | ■ | ■ | ■ |
| 200HPS, mogul | RB | RB | RB |
| 250HPS, mogul | RB | RB | RB |

■ Available. RB: Remote Ballast Required.

L80-L81-L82 Contemporary Lantern

Post Top

Optical System / HID

(Lamps not included)



RR Optics
Round borosilicate refractor

RR5 Symmetrical
RR3 Asymmetrical
RR3MD Asymmetrical with medium deflector



SE Optics
Hydro-formed cut-off reflector system set in faceted arc-image duplicating patterns



SE5 Symmetrical
SE3 Asymmetrical
> House shield available in option (HS)



RACE Optics
Round acrylic (max. 100w) or borosilicate (150w and more) refractor with segmented upright recovery dome

RACE5 Symmetrical
RACE3 Asymmetrical
RACE3D Asymmetrical with deflector

Finials



L80-L81-L82 Contemporary Lantern

Post Top


Adaptors



SF80




SF0




SFS



SF70




SF72




SF73


Mountings




CRA



CRC




CRD




CRF


Poles and Pole Options




APR4-LBC3



RA61



R80



RTA906/907

