




Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Complete fixture consists of the Trim and Frame-in Kit. Select each separately.

Reflector Trim		Frame-in Kit (Low Voltage)		Lamp	Voltage
394CHX	Chrome reflector and white flange	Remodeler Non-IC	300MRSPX	50W MR16 / 37W MR16 IR	120V
		Remodeler Non-IC	3401MREX	50W MR16 / 37W MR16 IR	120V
		Frame Non-IC	302MRLX	50W MR16 / 37W MR16 IR	120V
		Frame Non-IC	302MRSPX	50W MR16 / 37W MR16 IR	120V
		Frame Non-IC	302MREX	50W MR16 / 37W MR16 IR	120V
		Frame IC	302MRIC7SPX	50W MR16 / 37W MR16 IR	120V
		Frame IC	302MRIC9SPX	50W MR16 / 37W MR16 IR	120V
		Lytening Frame AirSeal®	302MRAICSPX	50W MR16 / 37W MR16 IR	120V
		Lytening Frame AirSeal®	302MRAICEX	50W MR16 / 37W MR16 IR	120V
Frame-in Kit (Line Voltage)		Lamp		Voltage	
Remodeler Non-IC	300ESX	50W ES/ESD16 (GU10)		120V	
Frame Non-IC	302ESX	50W ES/ESD16 (GU10)		120V	
Frame IC	302ESICX	50W ES/ESD16 (GU10)		120V	
Lytening Frame AirSeal®	302ESAICX	50W ES/ESD16 (GU10)		120V	
Frame-in Kit (HID)		Lamp		Voltage	
Remodeler Non-IC	3401MH39MRE1	39W MR16 (GX10) CMH		120V	

Features

Housing: 25 ga galvanized steel.

Residence Mounting Clips: Factory-installed; zinc plated spring steel; free-hand installation.

Flange Housing: Cold rolled steel 22ga.

Cone: 18ga aluminum. Chrome finish.

Adjustable Lampholder Support: 27 ga. Steel. rotates 358° horizontally and 0° to 35° vertically.

Mounting Clips (2): 24 ga. spring steel, zinc plated. Provides easy snap-in / snap-out action.

Lamp Guard: 2" (51mm) dia. clear soda lime glass.

Accessories

2" (51mm) dia. Glass Colour Filters: See ADF2 Specification Sheet.

2" (51mm) dia. Specialized Filters: See AF2 Specification Sheet.

Square Faceplates

300SQBK	Black
300SQWH	White

Marking

cCSAus Certified, suitable for damp locations.

Frame-in Kit

See Frame-In Kit specification sheets for more details.

