


Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_



Complete fixture consists of Reflector Trim & Power Pack. Select each separately.

Power Pack	Cut-out	Reflector Trim
302MREX (120V)	3 3/4" (95mm)	Accepts most 3-3/4" (95mm) 300 series trims; see Reflector Trim specification sheets.

## Features

- Mounting Frame:** 20ga. galvanized steel. Four slots are positioned 90° apart to simplify alignment.
- Mounting Bars:** (4) 18 ga. galvanized steel. 13" (330mm) long bars extend to 27" (686mm), rotatable and lockable, integral T-bar tabs. Spike detail eliminates the need of additional nailing.
- Mounting Bars Locking Clip:** (1) locks mounting bars in place.
- Snap-on Socket Cup:** 22ga. galvanized steel. Easy snap-on to housing.
- Socket:** Porcelain body ; Two-pin (GX5.3 base) Pre-wired with 18 ga. PTFE 250° leads to junction box.
- Transformer:** Electronic, 60VA, Class 2 Transformer, 120 volt primary, nominal 12 volt secondary, class "H".
- Junction Box:** 4" (102mm) x 3" (76mm) x 2" (51mm) 18 ga. galvanized steel. CSA/UL certified for maximum of 8 No. 12 ga. 90° C through branch circuit conductors. Integral cable clamp permit attachment of non metallic Loomex without need of additional connectors. Pry-out knock-outs accept BX cable. Easy access from both sides with snap-on covers.
- Thermal Protector:** Meets CSA/UL requirements. Insulation, if used, must be kept 3" (76mm) away from luminaire sides and junction box.

# 302MREX LytePoints 3 3/4"

## Non-IC Frame MR16

### Accessories

**Mounting Bars Extenders: 1964**

20" (508mm) long. Set of 2

**Mounting Bar Locking Clips: 0098**

To lock mounting bars in place after installation. Set of 12.

### Labels

Damp or Wet location rated depending on trim used.

