



LIGHTOLIER

by @signify

Track Lighting

Track Accessory

7619 Multipoint



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

example: 7619WH

Series	Finish
<input type="text"/>	<input type="text" value="WH"/>
7619 MultiPoint	WH White

Note: See fixture specification sheet for compatibility.

Features

- Basic Lytespan Track Strip:** Structural aluminum extrusion painted finished to match SKU color. Color coordinated plastic insulator securing copper conductors.
- Canopy:** Steel painted finished to match SKU color. Attached with two flush mount nickel plated screws.
- Crossbar:** 1/16" thick galvanized steel. Provides secure mounting of multipoint to electrical junction box.
- Supply leads:** 16ga. White and Black Insulated stranded copper wire, 18ga green insulated copper stranded wire.
- Mounting:** Wall or ceiling mount.

Electrical

Electrical rating: 1120V, 60Hz, 8amp MAX. All Lytespan Track luminaires are polarized and continuously grounded throughout. Electrical conductors are concealed in an insulating liner. Intended for wiring to branch circuit building wire with ground. All wiring must be in accordance with National and Local Codes. Use 90°C minimum supply wire to multipoint.

Labels

U.L. and cULus listed.

Warranty

3-year warranty
(visit philips.com/warranties for details).



@signify