

Shaper

DESCRIPTION

Circular and Radial forms are the theme of the Loop Series fixtures. The Loop Circular Pendants embody an angular white acrylic lens encased in a solid metal spinning. Behind the lens is a ring of LED sources providing indirect illumination on the lens. The resultant light effect is a stimulating glow that fades subtly toward the perimeter of the fixture. Aircraft cable mounting allows for easy installation and adjustment on site with an optional cable choke plate. A wide variety of finish options and LED color temperatures allows the designer to select a look that is right for many different settings.

SPECIFICATION FEATURES

Material

The outer housing is an aluminum spinning with steel and aluminum structure and aluminum heat sinks. The lens is vacuum formed white acrylic.

Finishes

ALP (Aluminum Paint)
 BM (Bronze Metallic)
 DP (Dark Platinum)
 GRM (Graphite Metallic)
 MB (Matte Black)
 MW (Matte White)
 CC (Custom Color – Specify)

LED

27" L10: 9000 source lumens at max 80W
 38" L15: 14,000 source lumens at max 120W

Driver

LED system coupled with electronic driver to deliver optimal performance. Electronic drivers are available for 120-277V applications. A 0-10V dimming standard on all models.

Installations

The Loop Circular Pendant is designed for mounting from a flush 4" round or octagonal j-box. Aircraft cable mounting provides site adjustment up to 48" or 96" OA (min OA is 18").

A flexible cord provides power to the fixture. Installation instructions are available on-line.

Compliance

All Autograph Collection products are UL and cUL approved for interior damp locations.

Catalog #		Type
Project		
Comments		Date
Prepared by		



AUTOGRAPH COLLECTION LOOP SERIES 845 LOOP PENDANT


Diameter: 27"

- Lumen Output Source Lumens: 9000 Nominal lumens
- Wattage: 80W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10v

Diameter: 36"

- Lumen Output Source Lumens: 14000 Nominal lumens
- Wattage: 120W
- Color Rendering: CRI 83+
- Correlated Color Temperature: 4000K, 3500K, 3000K, 2700K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10v

DIMENSIONS



ORDERING INFORMATION

Sample Number: 845-27-PSJCAC-L10/827-UNV-ALP-48

Series	Size	Mounting Type	LED Lamp		LED Voltage	Finish	Options	OA
			27"	36"				
845 = Loop Pendant	27=27"	PSJCAC=Pendant Aircraft Cable with Clear SJ Cord	L10/827	L15/827	UNV (120-277V)	ALP=Aluminum Paint MW=Matte White MB=Matte Black DP= Dark Platinum GRM=Graphite Metallic BM=Bronze Metallic CC=Custom Color - Specify	CCH =Cable Choke	48=48" Overall Height 96=96" Overall Height
	36=36"		PSJWAC=Pendant Aircraft Cable with White SJ Cord	L10/830 L10/835 L10/840				

