DESCRIPTION

The 143 series is a decorative pendant family with a circular form. This product is a drum shape shade, and also has a drum shade in shade option, with translucent materials, to highlight elegant spatial forms. The integral LED light engine is available in 2700K, 3000K, 3500K, and 4000K color temperatures that evenly illuminates the shade and the bottom lens, with 83+ CRI. The stem, canopy, and finial finishes are available in many painted options. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Heavy gauged steel frame, laminated styrene backing, and minimum internal structure. Shades come in three standard sizes, eleven standard fabrics, three vinyl materials, four printed wood patterns, and two translucent organza fabrics.

SPECIFICATION FEATURES

Construction

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover available (TC).

5" diameter canopy with self aligning swivel. Stem is 1/2" aluminum tubing with threaded rod. Air craft cable option is 3/64" cable. Slope adapter option available (SCA-XX - 8°- 45°, but slope dimension must be provided).

<u>24" Diameter</u> Standard length = 24" OAH (Overall Height)

Min	Max	
12" OAH	96" OAH	

30" Diameter

Standard length = 28" OAH (Overall Height)

Min	Max
IVIIII	Ινίαλ
14" OAH	96" OAH

<u>36" Diameter</u> Standard length -

Junuaru	iengui –
34" OAH ((Overall Height)

Min		Max		
	16" OAH	96" OAH		

Stem Options					
Single Rigid Stem	-P1S				
Single Stem Air Craft Cable	-P1SAC				
Concult footom, for non-standard					

Consult factory for non standard lengths under min and over 96".

Painted Finishes

(canopy, stem, and finial) ALP - Aluminum Paint BM - Bronze Metallic DP - Dark Platinum GRM - Graphite Metallic MB - Matte Black MW - Matte White CC - Custom Color – Specify Consult factory for cutom color.

Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl.

Fabric Shade Selections VLW - Verona Linen White SIW - Silk White SIY - Silk Ivory SWH - Shantung White SEG - Shantung Eggshell SBG - Shantung Beige GBB - Glynn Brussels Beige LOLA -Lola Sand NGS - Silk Glow LCK - Linen Chopstick LAT - Linen Alabaster

<u>Vinyl Coated Fabric</u> ABR - Alabaster Vinyl NFX - Natural Flax GHY - Golden Honey **Note:** For humid environments, such as showers or open lobbies, Vinyl Coated Fabrics are recommended.

LEDs LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated Lamp Life: 50,000 hrs

Catalog # Type Project Date Comments Date Prepared by Image: Comment set of the set of th

Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

Control

Standard driver is 0-10V with 10% dimming.

Compliance

Components are UL recognized and luminaires are cUL listed for 25° ambient environments. Fixtures are rated for damp location listing. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

Life and Warranty

Standard five-year warranty on all parts.

Wattage: 47W

CRI: 83+
CCT: 2700K, 3000K, 3500K, 4000K

• Delivered Lumens (@3500K): 4038

• CCT: 2700K, 3000K, 3500K, 4000K

Delivered Lumens (@3500K): 4038

143-P SERIES

Diameter: 36"

Diameter: 24"

Wattage: 47W

Diameter: 30"

• CRI: 83+

- Delivered Lumens (@3500K): 6894
- Wattage: 79W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K



ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)

Fixture Number: 143-24-P1S-L5/827-UNV-ALP-24

Series 1	Size	Mounting Type	LED	Lamp	LED Voltage	Finish (Canopy, Stem, Finial)	Options ²	Overall Height (OAH)
143 = Drum Pendant	24 = 24" 30 = 30" 36 = 36"	P1S = Single Stem P1SAC = Single Stem with Aircraft Cable	24" L5/827 L5/830 L5/835 L5/840 30" L5/837 L5/830 L5/835 L5/840	36" L9/827 L9/830 L9/835 L9/840	UNV (120-277)	MW = Matte White MB = Matte Black BM = Bronze Metallic DP = Dark Platinum ALP = Aluminum Paint GRM = Graphite Metallic CC = Custom Color specify	SCAXX = Sloped ceiling adapter TC = White acrlylic top	24 = 24" OAH 28 = 28" OAH 34 = 34" OAH XX" = custom length must be specified (143-24=12"-96' (143-34=16"-96'

Notes: ¹ Fabric shade not included. Please specify fabric shade from selections provided to complete fixture order. ² Sloped ceiling adapter can accommodate up to 8-45 degree slope. Slope dimension must be provided. ³ Shade in Shade option for Fabric selections only.



Shaper

ORDERING INFORMATION (Select FIXTURE NUMBER and SHADE NUMBER to complete specification)

Shade Number: 143-24-SHD-SIW-SIS-EDT

Series	Size	SHD	Finish	Outer Shade Material	
143 = Drum Shade	24 = 24" 30 = 30" 36 = 36"	SHD = Shade Fabric	Fabric: VLW = Verona Linen White GBB = Glynn Brussels Beig SIW = Silk White LOLA = Lola Sand SIY = Silk Ivory NGS = Silk Glow SWH = Shantung White LCK = Linen Chopstick SEG = Shantung Eggshell LAT = Linen Alabaster SBG = Shantung Beige Shantung Beige	Vinyl: ABR = Alabaster Vinyl NFX = Natural Flax GHY = Golden Honey	SIS-EDT = Top Square-in Shade, Earth Dust SIS-WMT =Top Square-in Shade, White Mist

DIMENSIONS



OPTIONS



TOP COVER (TC)



SLOPED CEILING ADAPTOR (SCA)



Cooper Lighting Solutions 18001 E. Colfax Avenue Denver, CO 80011 P: 800-760-1317 www.cooperlighting.com

Specifications and dimensions subject to change without notice.